





LOC		DIST		REVISIONS					
AD	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			T2	REVISED PER ECO-11-018809			15SEP11	KH	JO


- 1 REELED FOR MINI-APPLICATOR.
- 2 GOLD FLASH OVER NICKEL, .000015 GOLD ON CONTACT AREA.
- 3 GOLD FLASH OVER NICKEL, .000030 GOLD ON CONTACT AREA.
- 4 PREPLATED 0.00127-0.00381 (.000050-.000150) BRIGHT TIN.
- 5 .000050 NICKEL ON ENTIRE CONTACT, .000015 GOLD IN CONTACT AREA.
- 6 GOLD PLATING NOT REQUIRED IN THIS AREA.
- 7 SHEARED EDGES PERMITTED TO BE UNPLATED.
- 8 .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA, .000100-.000200 BRIGHT TIN LEAD IN AREA K.
- 9 GOLD FLASH OVER NICKEL, .000050 GOLD ON CONTACT AREA.
- 10 CUT OUTS ON BOX AT MANUFACTURER'S OPTION.
- 11 .000030 GOLD IN CONTACT AREA, .000100-.000200 BRIGHT TIN-LEAD IN AREA K, ALL OVER .000050 NICKEL.
- 12 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS).
- 13 .000030 GOLD IN CONTACT AREA, .000100-.000200 TIN IN AREA K, ALL OVER .000050 NICKEL.
- 14 .000050 NICKEL ENTIRE CONTACT, .000015 GOLD ON CONTACT AREA, .000100-.000200 TIN IN AREA K.




SECTION B-B



WIRE SIZE #22-#26
SECTION E-E



INSULATION RANGE .061 MAX
SECTION G-G



SECTION D-D

OBSOLETE	LOOSE PIECE	2 / 13 REF	6-87756-8
	REELED	2 / 13	6-87756-7
OBSOLETE	LOOSE PIECE	2 / 14 REF	6-87756-6
	REELED	2 / 14	6-87756-2
OBSOLETE	LOOSE PIECE	2 / 11 REF	1-87756-8
	REELED	2 / 11	1-87756-7
OBSOLETE	LOOSE PIECE	7 / 8 REF	1-87756-6
	LOOSE PIECE	9 REF	1-87756-4
OBSOLETE	REELED	7 / 8	1-87756-2
	REELED	9	1-87756-1
OBSOLETE	REELED	5 / 7	1-87756-0
	LOOSE PIECE	4 REF	87756-7
OBSOLETE	REELED	4	87756-6
	LOOSE PIECE	2 REF	87756-5
OBSOLETE	REELED	2	87756-4
	LOOSE PIECE	3 REF	87756-3
OBSOLETE	REELED	3	87756-2
	DESCRIPTION	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L.D.RINGLEY 12-10-85	 TE Connectivity	
DIMENSIONS: INCHES		CHK J. GESFORD 12-16-85		
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. PLC ± - 1. PLC ± - 2. PLC ± - 3. PLC ± .005 4. PLC ± - ± - ANGLES ± - ± -	APVD J. GESFORD 12-16-85	NAME	
		PRODUCT SPEC	CONTACT, FEMALE, MOD IV, CRIMP SNAP-IN	
		APPLICATION SPEC	-	
MATERIAL .008 THK CU-SN-P ALLOY 521	FINISH SEE TABLE	WEIGHT -	SIZE A1	CAGE CODE 00779
		DRAWING NO 87756	RESTRICTED TO -	REV T2
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1