Ordering number : ENN7121

P-Channel Silicon MOSFET

CPH3317

Ultrahigh-Speed Switching Applications


Features

- Low ON-resistance.
- Ultrahigh-speed switching.
- 2.5V drive.

Package Dimensions

unit : mm
2152A

[CPH3317]



1 : Gate
2 : Source
3 : Drain

SANYO : CPH3

Specifications

Absolute Maximum Ratings at Ta=25°C

Parameter	Symbol	Conditions	Ratings	Unit
Drain-to-Source Voltage	V_{DSS}		−20	V
Gate-to-Source Voltage	V_{GSS}		±10	V
Drain Current (DC)	I_D		−1	A
Drain Current (Pulse)	I_{DP}	PW≤10μs, duty cycle≤1%	−4	A
Allowable Power Dissipation	P_D	Mounted on a ceramic board (900mm²×0.8mm)	0.9	W
Channel Temperature	Tch		150	°C
Storage Temperature	Tstg		−55 to +150	°C

Electrical Characteristics at Ta=25°C

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	I_D=−1mA, V_{GS}=0	−20			V
Zero-Gate Voltage Drain Current	I_{DSS}	V_{DS}=−20V, V_{GS}=0			−1	μA
Gate-to-Source Leakage Current	I_{GSS}	V_{GS}=±8V, V_{DS}=0			±10	μA
Cutoff Voltage	$V_{GS}(off)$	V_{DS}=−10V, I_D=−1mA	−0.4		−1.4	V
Forward Transfer Admittance	$\|yfs\|$	V_{DS}=−10V, I_D=−500mA	0.84	1.2		S
Static Drain-to-Source On-State Resistance	$R_{DS}(on)1$	I_D=−500mA, V_{GS}=−4V		360	470	mΩ
	$R_{DS}(on)2$	I_D=−300mA, V_{GS}=−2.5V		520	730	mΩ

Marking : JS

Continued on next page.

■ Any and all SANYO products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your SANYO representative nearest you before using any SANYO products described or contained herein in such applications.

■ SANYO assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all SANYO products described or contained herein.


SANYO Electric Co.,Ltd. Semiconductor Company
TOKYO OFFICE Tokyo Bldg., 1-10, 1 Chome, Ueno, Taito-ku, TOKYO, 110-8534 JAPAN


Downloaded from Arrow.com.


Continued from preceding page.


Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	
Input Capacitance	Ciss	V_{DS}=–10V, f=1MHz		115		pF
Output Capacitance	Coss	V_{DS}=–10V, f=1MHz		23		pF
Reverse Transfer Capacitance	Crss	V_{DS}=–10V, f=1MHz		15		pF
Turn-ON Delay Time	t_{d}(on)	See specified Test Circuit.		8		ns
Rise Time	t_{r}	See specified Test Circuit.		6		ns
Turn-OFF Delay Time	t_{d}(off)	See specified Test Circuit.		15		ns
Fall Time	t_{f}	See specified Test Circuit.		7		ns
Total Gate Charge	Qg	V_{DS}=–10V, V_{GS}=-4V, I_{D}=-1A		1.5		nC
Gate-to-Source Charge	Qgs	V_{DS}=–10V, V_{GS}=-4V, I_{D}=-1A		0.4		nC
Gate-to-Drain “Miller” Charge	Qgd	V_{DS}=–10V, V_{GS}=-4V, I_{D}=-1A		0.3		nC
Diode Forward Voltage	V_{SD}	I_{S}=–1A, V_{GS}=0		–0.89	–1.5	V


Switching Time Test Circuit
















Downloaded from Arrow.com.

















Downloaded from Arrow.com.

Note on usage : Since the CPH3317 is designed for high-speed switching applications, please avoid using this device in the vicinity of highly charged objects.

- Specifications of any and all SANYO products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- SANYO Electric Co., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all SANYO products(including technical data,services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of SANYO Electric Co., Ltd.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the SANYO product that you intend to use.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. SANYO believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

This catalog provides information as of November, 2001. Specifications and information herein are subject to change without notice.

Downloaded from Arrow.com.