


Small Signal Product

Bi-directional ESD Protection Diode

FEATURES

- Meet IEC61000-4-2 (ESD) $\pm 15\text{kV}$ (air), $\pm 8\text{kV}$ (contact)
- Protects one Bi-directional I/O line
- Low clamping voltage
- Working Voltage : 5, 12 and 24V
- High component density
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21



0603-B



MECHANICAL DATA

Case: 0603-B standard package molded plastic

Terminals: Gold plated, solderable per MIL-STD-750, method 2026

Weight: 3 mg (approximately)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)							
PARAMETER		CONDITIONS	SYMBOL	MIN	TYP	MAX	UNIT
Diode breakdown voltage	TESDUB5V0	IR=1mA	V _{BO}	5.1	7	-	V
	TESDUB12V			13	17	-	
	TESDUB24V			25	28	-	
Leakage current	TESDUB5V0	VR=5V	I _L	-	0.1	2	μA
	TESDUB12V	VR=12V		-	-	-	
	TESDUB24V	VR=24V		-	-	-	
Junction capacitance	TESDUB5V0	VR=0V, f=1MHz	C _T	-	15	20	pF
	TESDUB12V			-	12	-	
	TESDUB24V			-	10	-	
ESD capability		IEC 61000-4-2 (air) IEC 61000-4-2 (contact)	ESD	-	-	15	KV
				-	-	8	
Clamping voltage	TESDUB5V0	I _{PP} =5A, T _P =8/20μs	V _C	-	-	15	V
	TESDUB12V	I _{PP} =1A, T _P =8/20μs		-	-	25	
	TESDUB24V	I _{PP} =1A, T _P =8/20μs		-	-	47	
Peak pulse power	TESDUB5V0	T _P =8/20μs	P _{PP}	-	-	75	W
	TESDUB12V			-	-	25	
	TESDUB24V			-	-	47	
Junction temperature range			T _J	-55 to +125			°C
Storage temperature range			T _{STG}	-55 to +150			°C





Small Signal Product

ORDERING INFORMATION				
PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
TESDUBxxx (Note 1, 2)	RG	G	0603-B	4K / 7" Reel

Note 1: "xxx" defines voltage from 5V (TESDUB5V0) to 24V (TESDUB24V)
 Note 2: Whole series with green compound


EXAMPLE				
EXAMPLE P/N	PART NO.	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
TESDUB5V0 RGG	TESDUB5V0	RG	G	Green compound

RATINGS AND CHARACTERISTICS CURVES
 (T_A=25°C unless otherwise noted)




Small Signal Product

DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	1.60	1.80	0.063	0.071
B	0.80	1.00	0.031	0.039
C	0.30	0.45	0.012	0.018
D	0.70	0.85	0.028	0.033
E	0.65	0.75	0.026	0.030
F	0.28	0.35	0.011	0.014

SUGGESTED PAD LAYOUT



DIM.	Unit (mm)
G	0.80
X	0.60
X1	2.00
Y	0.80

MARKING

Part No.	Marking
TESDUB5V0	E05
TESDUB12V	E12
TESDUB24V	E24

Not Recommended

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.