





REVISIONS					
#	LTR	DESCRIPTION	DATE	DWN	APVD
A2		ECR-25-238910	09APR2025	ABS	PS



SECTION Z-Z
ROTATED 90° CW



RECOMMENDED P.C. BOARD HOLE LAYOUT

- △ HOUSING: GLASS-FILLED NYLON.
- △ POST: COPPER ALLOY.
- △ POST FINISH: 0.00076 [.000030] GOLD IN AREA G, 0.00254-0.00508 [.000100-.000200] BRIGHT TIN-LEAD IN AREA H, ALL OVER 0.00127 [.000050] NICKEL.
- △ POINT OF MEASUREMENT FOR PLATING THICKNESS.
- △ RECESSED DATE CODE.
- 6. CSA LOGO HOT STAMPED WHITE ON HOUSING.
- △ POST FINISH: 0.00076 [.000030] GOLD IN AREA G, 0.00254-0.00508 [.000100-.000200] MATTE TIN IN AREA H, ALL OVER 0.00127 [.000050] NICKEL.
- △ ROHS 2002/95/EC COMPLIANT.

SUPERSEDED BY 5-147343-1

REV	DESCRIPTION	DATE	DWN	APVD	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
7	1-5,7,9,11,13 15,17,19,21	2,4-21	73.15 [2.880]	70.36 [2.770]	71.12 [2.800]	24	18/50	△ 5-147343-1
3	1-5,7,9,11,13 15,17,19,21	2,4-21	73.15 [2.880]	70.36 [2.770]	71.12 [2.800]	24	18/50	147343-1
FINISH		POST OMITTED	K	J	B	A	NO OF POSN	PART NUMBER
THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN S. HAYMAKER OSNOV99	TE Connectivity				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME: J. GESFORD PRODUCT SPEC: J. GESFORD APPLICATION SPEC:				
mm [INCHES]	0 PLC ± -	1 PLC ± -	2 PLC ± -	3 PLC ± 0.13 [.005]	4 PLC ± -	ANGLE		SEE TABLE
MATERIAL		FINISH		WEIGHT		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF 1 REV A2
△ 1 △ 2		SEE TABLE		A1 00779		C-147343		