




3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS





NOTES:


1. MATERIALS:
- | | | |
|--------------|---------------|---------------|
| SPRINGS | SS | PLATING : Au |
| CONTACTS | Be Cu | COLOR : BLACK |
| IC GUIDES | PES | COLOR : BLACK |
| PRESSURE PAD | PES | COLOR : BLACK |
| COVER | PPS or equiv. | COLOR : BLACK |
| BASE | PES | COLOR : BLACK |
2. SEE THE REGULATORY INFORMATION APPENDIX (RIA) IN THE "RoHS COMPLIANCE" SECTION WWW.3MCONNECTOR.COM FOR COMPLIANCE INFORMATION (RIA E1 & C1 APPLY).
3. FOR PRODUCT SPECIFICATIONS AND WARRANTY INFORMATION SEE: WWW.3MCONNECTOR.COM PN 288-4205-01

DESIGN REFERENCE		NEXT ASSEMBLY		A 37213 INITIAL RELEASE		ARM
DISTRIBUTION CODES		SCALE 5 1		REV ECO	ISSUE DATE AND DESCRIPTION	DRFT
DIVISION		TOLERANCES EXCEPT AS NOTED		CHKD	DATE	DATE
DO NOT SCALE DRAWING		INCHES .0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002		3M 3M Center St. Paul, MN 55144		DATE
THIRD ANGLE PROJECTION		MILLIMETERS 0 ± .0 .00 ± .000 ± .0000 ± .0002		© 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.		DATE
MAX SURFACE ROUGHNESS 125 ✓		INTERPRET PER ASME Y14.5 - 1994		QFN TEST SOCKET, 0.4mm, 88 POS, EVEN ROW, 10X10 PKG, WITH TP		DATE
CAGE NUMBER		SIZE		DRAWING NO. 78-5100-2464-5		REV. A
MODEL		TEXTTOOL - QFN		DET. LISTS		SHT 1 OF 2

3M™ TEXTTOOL™ OPEN-TOP SOCKETS FOR QFN APPLICATIONS



RECOMMENDED IC (REF.)

DESIGN REFERENCE				NEXT ASSEMBLY				REV	ECO	ISSUE DATE AND DESCRIPTION				DRFT	CHKD
DISTRIBUTION CODES								DRFT	DATE			MFG		DATE	
								CHKD	DATE			APPVL		DATE	
DIVISION				DIVISION CODE				3M Center St. Paul, MN 55144 © 3M COPYRIGHT 2012 This document is the copyrighted property of the 3M Company and may not be reproduced without 3M written permission or used for other than 3M authorized purposes.							
DO NOT SCALE DRAWING				SCALE 5 1											
				INCHES				TITLE QFN TEST SOCKET, 0.4mm, 88 POS, EVEN ROW, 10X10 PKG, WITH TP							
				.0 ± .1 .00 ± .02 .000 ± .005 .0000 ± .0002											
THIRD ANGLE PROJECTION				MILLIMETERS				CAGE NUMBER DRAWING NO. REV.							
INTERPRET PER ASME Y14.5 - 1994				0 ± .1 .0 ± .005 .00 ± .0002											
MAX SURFACE ROUGHNESS				ANGLES ± 1°				CAGE NUMBER C			DRAWING NO. 78-5100-2464-5			REV. A	
125 ✓ ☑ MARKED ONLY								LISTS			YES NO			SHT 2 OF 2	
MODEL								TEXTTOOL - QFN			DET. LISTS				