


BR-2/3A

BR Cylindrical-type Lithium Battery



Features & Benefits

- Long-term operating performance
- Suitable for Power supplies for products such as that demand long-term reliability

Specifications


Nominal voltage		3V
Nominal capacity		1,200mAh
Continuous drain		2.5mA
Dimensions* ¹	Diameter(Max.)	17.0mm
	Height(Max.)	33.5mm
Weight* ¹		Approx. 13.0g
Operating temperature		-40°C ~ +85°C

*¹ Without tabs.

Applications

Commercial equipment (communication/measurement devices), meters (gas, water, electricity, hot water), memory backup (large FA equipment), automotive electronic components (security alarms), etc.

Discharge temperature characteristics



Operating voltage vs. Discharge current (voltage at 50% discharge depth)

