



**Data Sheet | Item Number: 280-502/281-604**  
Component terminal block; double-deck; with direct connection to DIN rail; with P6KE91C TVS diode; 60 VDC; for DIN-rail 35 x 15 and 35 x 7.5; 2.5 mm²; CAGE CLAMP®; gray  
<https://www.wago.com/280-502/281-604>




Color: ■ gray

Similar to illustration



Similar to illustration



**Short description:**  
WAGO's component terminal block with single-stage surge suppression device and direct connection to DIN-35 rail is equipped with a TVS diode.

**Features:**

- Protect your system against overvoltage
- Slim, space-saving design
- Control operational costs by preventing expensive, unplanned downtime
- High operational reliability and system uptime

Notes	
Safety Information	<ul style="list-style-type: none"><li>- Installation must be performed by qualified personnel only.</li><li>- The DIN-rail must be grounded.</li><li>- The input current must be protected by a suitable fuse.</li><li>- Protection against contact with stored charges must be ensured.</li><li>- Do not insert or remove pluggable modules when energized.</li><li>- The IP20 protection rating must be maintained in the assembled state or when using an end/intermediate plate compatible with the rail-mount terminal block.</li></ul>



Electrical data		
Nominal operating voltage		60 VDC
Maximum continuous voltage		77 VDC
Rated continuous current		20 A
Nominal discharge current (10/1000 µs) (line)		4.8 A
Protection level (10/1000 µs)		≤ 125 VDC
Capacitance		≤ 550 pF

Connection data		
Connections (number)		2
Connection technology		CAGE CLAMP®
Solid conductor		0.08 ... 2.5 mm² / 28 ... 14 AWG
Fine-stranded conductor		0.08 ... 2.5 mm² / 28 ... 14 AWG
Strip length		8 ... 9 mm / 0.31 ... 0.35 inches

Physical data		
Width		5 mm / 0.197 inches
Height		64 mm / 2.52 inches
Depth from upper-edge of DIN-rail		58.5 mm / 2.303 inches

Mechanical data		
Design		with direct connection to DIN-rail
Mounting type		DIN-35 rail

Material data		
Color		gray
Insulation material (main housing)		Polyamide (PA66)
Material group		I
Flammability class per UL94		V0
Fire load		0.173 MJ
Weight		8.5 g

Environmental requirements		
Processing temperature		-35 ... +85 °C

Commercial data		
Product Group		1 (Rail Mounted Terminal Blocks)
PU (SPU)		50 pcs
Packaging type		Box
Country of origin		DE
GTIN		4017332225069
Customs tariff number		85369010000



Product Classification		
UNSPSC		39121410
eCl@ss 10.0		27-14-11-27
eCl@ss 9.0		27-14-11-27
ETIM 9.0		EC000903
ETIM 8.0		EC000903
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,With Exemption
RoHS Exemption		7(a) 7(c)-I

Downloads		
Environmental Product Compliance		
Compliance Search		
Environmental Product Compliance		
280-502/281-604		

Documentation				
Bid Text				
280-502/281-604	19.02.2019	xml	3.28 KB	
280-502/281-604	11.02.2015	doc	25.00 KB	

CAD/CAE-Data				
CAD data			CAE data	
2D/3D Models			EPLAN Data Portal	
280-502/281-604			280-502/281-604	
			WSCAD Universe	
			280-502/281-604	
			ZUKEN Portal	
			280-502/281-604	



1 Compatible Products

1.1 Required Accessories

1.1.1 End plate

1.1.1.1 End plate



**Item No.: 280-340**  
End and intermediate plate; 2.5 mm thick; gray



**Item No.: 280-341**  
End and intermediate plate; 2.5 mm thick; orange

1.2 Optional Accessories

1.2.1 Insulation stop

1.2.1.1 Insulation stop



**Item No.: 280-470**  
Insulation stop; 0.08 - 0.2 mm<sup>2</sup> "s" (0.14 mm<sup>2</sup> "f-st"); 5 pieces/strip; white



**Item No.: 280-471**  
Insulation stop; 0.25 - 0.5 mm<sup>2</sup>; 5 pieces/strip; light gray



**Item No.: 280-472**  
Insulation stop; 0.75 - 1 mm<sup>2</sup>; 5 pieces/strip; black

1.2.2 Jumper

1.2.2.1 Jumper



**Item No.: 280-490**  
Jumper; 10-way; insulated; gray



**Item No.: 280-482**  
Jumper; 2-way; insulated; gray



**Item No.: 280-492**  
Jumper; 2-way; insulated; gray



**Item No.: 280-483**  
Jumper; 3-way; insulated; gray



**Item No.: 280-484**  
Jumper; 4-way; insulated; gray



**Item No.: 280-485**  
Jumper; 5-way; insulated; gray

1.2.3 Marking

1.2.3.1 Marker



**Item No.: 793-502**  
WMB marking card; as card; MARKED; 1 ... 10 (10x); not stretchable; Horizontal marking; snap-on type; white



**Item No.: 793-503**  
WMB marking card; as card; MARKED; 11 ... 20 (10x); not stretchable; Horizontal marking; snap-on type; white



**Item No.: 793-504**  
WMB marking card; as card; MARKED; 21 ... 30 (10x); not stretchable; Horizontal marking; snap-on type; white



**Item No.: 793-505**  
WMB marking card; as card; MARKED; 31 ... 40 (10x); not stretchable; Horizontal marking; snap-on type; white



**Item No.: 793-506**  
WMB marking card; as card; MARKED; 41 ... 50 (10x); not stretchable; Horizontal marking; snap-on type; white



**Item No.: 793-501**  
WMB marking card; as card; not stretchable; plain; snap-on type; white



**Item No.: 2009-115**  
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



1.2.4 Tool

1.2.4.1 Operating tool



Item No.: 210-720  
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured