

- Products
- Solutions
- Technologies
- Support
- How To Buy
- Partners
- About Elo
- Resources

AccuTouch

- [Touchscreens](#) (current)
- [touchmonitors](#)
- [touchcomputers](#)

AccuTouch Controller

- [2216](#) (current)

AccuTouch technology

- [Specifications](#)

Support

- [Driver Download](#)

[Home](#) > [Products](#) > [Touchscreens](#) > [AccuTouch](#) >

AccuTouch COACH IV Chip Custom Controller

The COACH IV (Controller On A Chip, fourth generation) (Part #E775468, RoHS Compliant) is a compact universal resistive touchscreen controller chip solution. It supports both serial and USB communication interfaces and is capable of interfacing to either AccuTouch five-wire resistive touchscreens. Regardless of the configuration, operation is automatically detected on power up and needs no user intervention. The COACH IV fully supports the Elo SmartSet protocol and all program drivers, both serial and USB.

Quick Links

- ▶ [Differences between COACH III and COACH IV](#) (115K PDF)
- ▶ [Differences between COACH II and COACH IV](#) (143K PDF)

Features

- Single chip ASIC design for compact integration
- Supports both USB and RS232 interfaces with autodetection
- Serial Interface:
 - bidirectional communication as a DCE
 - 9,600 and 19,200 baud rates supported
 - Frame configuration 8 data, 1 stop, No Parity, Full Duplex
 - Software or hardware handshaking supported: XON/XOFF; DSR, DTR, RTS, CTS
- USB Interface:
 - Full speed USB device
 - Self-powered
- Supports Five wire touchscreens with autodetection
- Resolution: 4096x4096, size independent
- Conversion time approximately 10 ms per coordinate set
- Improved measurement algorithm eliminates the need for touch filter adjustments
- Full AccuTouch SmartSet protocol.
- Multiple output formats: Binary or ASCII
- E261-280, E271-140, E281A-4002 compatibility modes
- On-board calibration, coordinate scaling, and programmable output rates allow for application-specific performance tuning
- Configuration parameters including serial number are storable in off-chip NVRAM (EEPROM)
- Power requirements: 5 VDC, nominal (4.00 min, 5.25 max); 30 mA, typical
- 64-pin LQFP package (12 mm x 12 mm x 1.6 mm)
- Temperature:
 - Operating: -20°C to +85°C
 - Storage: -40°C to +125°C
- ESD rating (human body model): 2.0 kV
- Look up [product statement of compliance](#) by part number
- [RoHS Certificate of Compliance for COACH products](#)



 [Print Page](#)

Elo Touch Solutions Quick Links

[Contact Us](#)
[Careers at Elo](#)
[Languages](#)
[Site Map](#)
[Newsletter](#)

Resources Quick Links

[Warranty Policies](#)
[Locate a Reseller](#)
[Find Documents & Drawings](#)

Legal

[Terms of Sale](#)