

Representative Image

Catalog No. TY5234M

Description: CBL TIE 18LB 14IN NATURAL NYLON

UPC No 786210830780

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 357mm (14 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1.1mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds)

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Stainless Steel Barb
Tensile Strength	18 pounds , 80 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405

Dimensions

Width	0.09 in , 2.3 mm
Length	14 in , 357 mm
Thickness	0.04 in , 1 mm
Bundle Diameter	0.06 to 4.2 in , 1.5 to 102 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

by ABB

Downloaded from Arrow.com.

ETIM	EC000046 Cable tie
Band width	2.3 mm
Band width	0.09 inch
Length belt/tape/tie	357 mm
Length belt/tape/tie	14 inch
Tie thickness	1 mm
Tie thickness	0.04 inch
Max. bundle diameter	102 mm
Max. bundle diameter	4.02 inch
Min. holding force	80 N
Operation temperature	-60-+85 °C
Operation temperature	-76-+185 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E49405	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.