HellermannTyton

Technical data sheet

Article number:
305-04809 HFT-A-4.8/2.4



Product Group	Heat shrinkable tubing 2:1 - flexible and coloured
Product Family	HFT-A - self extinguishing
Material	Polyolefin, cross-linked (PO-X)
Colour	White (WH)

Behaviour at low Temperature test method	not cracking [IEC 60684-2]
Dielectric Strength [Test method]	21 kV/mm [IEC 60684-2]
Elongation at break (min.) [Test method]	400 % [IEC 60684-2]
Flammability	UL 224 VW-1
Heat Shock Elongation	390 %
Heat Shock Tensile Strength	13 MPa
Heat Shock Test	4h/200°C
Insulation Class	B (VDE 0530)
Longitudinal Change After Shrinkage	-5% max.
Min. Shrink Temperature - °C	+135 °C
Operating Temperature	-55 °C to +135 °C
Package Content	75 m
Package Content packed in	meter
Recov. Ø d max.	2.4 mm
Shrink Ratio	2:1
Specifications	CLASS 903201, UL 224, VG 95343-5:2016-10
Supplied Ø D min.	4.8 mm
Tensile Strength [Test method]	14 MPa [IEC 60684-2]
UL-File Number	E143529
Wall (WT)	0.50 mm

RoHS

created on 23. October 2026, 3:33 am

Technical changes and errors reserved. It's up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.