


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F3	REVISED PER ECN-21-127537	23NOV2021	RK	CDS

D

D



1. MATERIAL:
BODY: SEE TABLE
SLEEVE: COPPER PER ASTM B152
INSULATION: POLYAMIDE 6/6 (NYLON) PER ASTM D4066

MATERIAL:
CUERPO: VER TABLA
MANGA: COBRE POR ASTM B152
AISLAMIENTO: POLIAMIDA 6/6 (NYLON) POR ASTM D4066

2. FINISH:
BODY: TIN PLATE 0.002 [.000079]
MIN EXT THICK PER ASTM B545
SLEEVE: NONE
INSULATION COLOR: BLUE


TERMINAR:
CUERPO: HOJA DE HOJALATA 0.002 [.000079]
ESPESOR MÍNIMO EXT. POR ASTM B545
MANGA: NINGUNA
COLOR DE AISLAMIENTO: AZUL

3. WIRE RANGE: 1.000 [.039]–2.000 [.079]mm² [17–14 AWG]
GAMA DE ALAMBRE: 1.000 [.039] –2.000 [.079] mm² [17–14 AWG]

4. DIMENSION APPLIES TO ZONE C FOR A DISTANCE
OF 8.620 – 8.750 [.339 – .344]

C

C




B

B

LOOSE PIECE PIEZA SUELTA	100	BRASS PER ASTM B36 LATÓN POR ASTM B36	735159
PACKAGE TYPE TIPO DE PAQUETE	QTY CANTIDAD	BODY MATL. CUERPO MATL.	PART NUMBER NÚMERO DE PIEZA

A

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI S CHK DANIEL ROHDE APVD DANIEL ROHDE PRODUCT SPEC — APPLICATION SPEC — WEIGHT —		15NOV2019 15NOV2019 15NOV2019		TE Connectivity				
DIMENSIONS: mm [INCHES]		 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± 0.500 [.019] 4 PLC ± — ANGLES ± —		NAME		FULLY INSULATED FASTON RCPT 6.35 MM (BLUE) RECEPTÁCULO FASTON 6.35 MM AISLADO (AZUL) —				
MATERIAL SEE TABLE				FINISH 		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
						A3	00779	C-735159	—	
						CUSTOMER DRAWING				
						SCALE	5:1		SHEET	1 OF 1