

DATA SHEET

MMBD914

SURFACE MOUNT SWITCHING DIODE

VOLTAGE	100 Volts	POWER	225 mWatts
----------------	------------------	--------------	-------------------

FEATURES

- Very fast reverse recovery ($T_{rr} < 2.0$ ns typical)
- Low capacitance (4pF @ 0V typical)
- Surface mount package ideally suited for automatic insertion
- Lead free in comply with EU RoHS 2002/95/EC directives.
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

Case: SOT-23, Plastic


Terminals: Solderable per MIL-STD-750, Method 2026

Approx. Weight: 0.008 gram

Marking: T1

SOT-23

Unit : inch(mm)




ABSOLUTE RATINGS

PARAMETER	Symbol	Value	Units
Maximum Reverse Voltage	V_R	100	V
Peak Reverse Voltage	V_{RRM}	100	V
Continuous Forward Current	I_F	0.2	A
Non-repetitive Peak Forward Surge Current at $t=1.0$ us	I_{FSM}	4.0	A

THERMAL CHARACTERISTICS


PARAMETER	Symbol	Value	Units
Power Dissipation (Note 1)	P_{TOT}	225	mW
Thermal Resistance, Junction to Ambient (Note 1)	$R_{\theta JA}$	556	$^{\circ}C/W$
Junction Temperature	T_J	-55 to 150	$^{\circ}C$
Storage Temperature	T_{STG}	-55 to 150	$^{\circ}C$

Note 1. FR-5 Board = 1.0x0.75x0.062 in.



ELECTRICAL CHARACTERISTICS (T_J=25°C, unless otherwise noted)

PARAMETER	SYMBOL	TEST CONDITION	MIN.	TYP.	MAX.	UNIT
Reverse Breakdown Voltage	V _(BR)	I _R =100uA	100	-	-	V
Reverse Current	I _R	V _R =20V	-	-	0.025	uA
		V _R =75V	-	-	5.0	
Forward Voltage	V _F	I _F =10mA	-	-	1.0	V
Total Capacitance	C _T	V _R =0V, f =1MHz	-	-	4.0	pF
Reverse Recovery Time (Figure 1)	T _{RR}	I _F =I _R =10mA, R _L =100Ω	-	-	4.0	ns



- Notes: 1. A 2.0kΩ variable resistor adjusted for a forward current (I_F) to 10mA
2. Input pulse is adjusted to I_{R(peak)} is equal to 10mA

Figure 1. REVERSE RECOVERY TIME EQUIVALENT TEST CIRCUIT

ELECTRICAL CHARACTERISTICS CURVE




Fig. 2. Reverse Current vs. Reverse Voltage




Fig. 3. Forward Current vs. Forward Voltage





Fig. 4. Capacitance vs. Reverse Voltage

MOUNTING PAD LAYOUT



ORDER INFORMATION

- Packing information
 - T/R - 12K per 13" plastic Reel
 - T/R - 3K per 7" plastic Reel



Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation. Customers are responsible in comprehending the suitable use in particular applications. Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.



Part No_packing code_Version

MMBD914_R1_00001

MMBD914_R2_00001

For example :

RB500V-40_R2_00001

Part No.

Serial number

Version code means HF

Packing size code means 13"

Packing type means T/R

Packing Code XX				Version Code XXXXX		
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code
T/B	A	N/A	0	HF	0	serial number
T/R	R	7"	1	RoHS	1	serial number
B/P	B	13"	2			
T/P	T	26mm	X			
TRR	S	52mm	Y			
TRL	L	PBCU	U			
FORMING	F	PBCD	D			