




- Features:**
- Switched-mode power supply with PowerBoost and TopBoost
 - Switch off the output and minimize power consumption via stand-by input
 - Output monitoring via DC OK contact
 - Suitable for both parallel and series operation
 - Natural convection cooling when horizontally mounted
 - Encapsulated for use in control cabinets
 - Electrically isolated output voltage (SELV) per UL 60950-1; PELV per EN 60204

Technical data			
Input		Output	
Phases	1	Nominal output voltage $U_{o\ nom}$	48 VDC (SELV)
Nominal input voltage $U_{i\ nom}$	1 x 100 ... 240 VAC	Output voltage range	33 ... 52 VDC (adjustable)
Input voltage range	1 x 85 ... 264 VAC; 120 ... 300 VDC	Default Setting	DC 48 V
Input voltage derating	-1.5 %/V (< 110 VAC)	Nominal output current $I_{o\ nom}$	10 A (48 VDC)
Nominal mains frequency range	50 ... 60 Hz; 0 Hz	Nominal output power	480 W
Input current I_i	≤ 2.3 A (230 VAC; 10 ADC)	Deviation	≤ 1 %
Discharge current	≤ 1 mA	Residual ripple	≤ 70 mV (peak-to-peak)
Inrush current	≤ 8 A (active power factor correction (PFC))	Current limitation	1.1 x $I_{o\ nom}$ (typ.)
Power factor correction (PFC)	Active	Overload behavior	TopBoost/PowerBoost/Constant current mode
Mains failure hold-up time	≥ 20 ms (230 VAC)	PowerBoost	DC 17.5 A (4 s); DC 15 A (8 s)
		TopBoost	60 ADC (25 ms)

Signaling and communication	
Signaling	1 x DC OK LED (green) 1 x Error LED (red) 1 x Stand-by input 1 x DC OK relay contact (changeover contact)
Operation status indicator	Green LED (DC OK) Red LED (error)

Efficiency/power losses	
Power loss P_i	≤ 0.8 W (standby); ≤ 4.8 W (no load); ≤ 43.2 W (nominal load)
Efficiency (typ.)	91 %



Circuit protection	
Internal fuse	T 10 A / 250 VAC
Pre-fuse (required)	An external DC fuse is required for the DC input voltage.
Backup fuse (recommended)	Circuit breaker: 6 A, 10 A, 16 A; Tripping characteristic: B or C

Safety and protection	
Isolation voltage (pri.-sec.)	DC 4.242 kV
Isolation voltage (pri.-PE)	DC 2.2 kV
Isolation voltage (sec.-PE)	0.7 kVDC
Protection class	I
Protection type	IP20; Per EN 60529
Resistance to reverse feed	≤ 63 VDC
Overvoltage category	II
Pollution degree	2
Transient suppression (primary)	Varistor
Short-circuit-protected	Yes
Open-circuit-proof	Yes
Parallel operation	Yes
Series operation	Yes
MTBF	> 500,000 h (per IEC 61709)

Connection data			
Connection 1		Connection 2	
Connection type	Input	Connection type	Output
Connection technology	CAGE CLAMP®	Connection technology	Push-in CAGE CLAMP®
WAGO connector	WAGO 231 Series	WAGO connector	WAGO 831 Series
Solid conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG	Solid conductor	0.5 ... 10 mm² / 20 ... 8 AWG
Fine-stranded conductor	0.08 ... 2.5 mm² / 28 ... 12 AWG	Fine-stranded conductor	0.5 ... 10 mm² / 20 ... 8 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches	Strip length	13 ... 15 mm / 0.51 ... 0.59 inches

Connection 3	
Connection type	Signaling
Connection technology	CAGE CLAMP®
WAGO connector	WAGO 733 Series
Solid conductor	0.08 ... 0.5 mm² / 28 ... 20 AWG
Fine-stranded conductor	0.08 ... 0.5 mm² / 28 ... 20 AWG
Strip length	5 ... 6 mm / 0.2 ... 0.24 inches

Physical data	
Width	97 mm / 3.819 inches
Height	171 mm / 6.732 inches
Depth from upper-edge of DIN-rail	187 mm / 7.362 inches
Note (dimensions)	Height with connector



Mechanical data		
Mounting type		DIN-35 rail
Material data		
Fire load		0 MJ
Weight		2460 g
Environmental requirements		
Ambient temperature (operation)		-25 ... +70 °C (Device starts at -40 °C (type-tested))
Ambient temperature (storage)		-25 ... +85 °C
Relative humidity		5 ... 96 % (no condensation permissible)
Derating		-3 %/K (> 50 °C)
Climatic category		3K3 (per EN 60721)
Standards and specifications		
Conformity marking		CE
Standards/specifications		EN 61010-1 EN 61010-2-201 EN 61204-3 EN 61558-2-16 UL 60950 UL 508
Commercial data		
Product Group		6 (INTERFACE ELECTRONIC)
PU (SPU)		1 pcs
Packaging type		Box
Country of origin		DE
GTIN		4050821226451
Customs tariff number		85044083900
Product Classification		
UNSPSC		39121004
eCl@ss 10.0		27-04-07-01
eCl@ss 9.0		27-04-07-01
ETIM 9.0		EC002540
ETIM 8.0		EC002540
ECCN		NO US CLASSIFICATION
Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03078
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081
UL Underwriters Laboratories Inc.	UL 508	E255817
UR Underwriters Laboratories Inc.	UL 60950-1	E255815

Declarations of conformity and manufacturer's declarations

Approval	Standard	Certificate Name
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 787-835



Documentation

Bid Text
787-835
04.07.2019
docx 22.31 KB
↓
787-835
04.07.2019
xml 7.25 KB
↓

Instruction Leaflet
Primär getaktete Stromversorgungen PRO
pdf 247.20 KB
↓

CAD/CAE-Data

CAD data
2D/3D Models 787-835



CAE data
EPLAN Data Portal 787-835
↓
WSCAD Universe 787-835
↓
ZUKEN Portal 787-835
↓



Engineering-Software				
Configuration and Commissioning Software				
WAGO Line Length Calculation	1.3.5 09.12.2019	exe 329.50 KB		

1 Compatible Products

1.1 Optional Accessories

1.1.1 Marking

1.1.1.1 Marker



Item No.: 2009-145
Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 248-501
Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 793-5501
WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 - 5.2 mm; plain; snap-on type; white



Item No.: 793-501
WMB marking card; as card; not stretchable; plain; snap-on type; white



Item No.: 2009-115
WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

1.1.1.2 Marking strip



Item No.: 2009-110
Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white



Item No.: 210-831
Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive; white



Item No.: 210-832
Marking strips; on reel; 3 mm wide; plain; Self-adhesive; white

1.1.2 Mounting adapter

1.1.2.1 DIN-rail adapter



Item No.: 787-897
Carrier rail adapter made of zinc die-cast; for mounting 787-8xx devices to a DIN 35 rail; gray



Item No.: 787-896
Carrier rail adapter; for mounting 787-8xx devices to a DIN 35 rail; gray

1.1.2.2 Wall-mount adapter



Item No.: 787-895
Mounting carrier; for screw fixing of 787-8xx devices on mounting plate or wall without DIN 35 rail; gray



1.1.3 Tool

1.1.3.1 Operating tool



[Item No.: 210-719](#)
Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft



[Item No.: 210-720](#)
Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured



[Item No.: 210-721](#)
Operating tool; Blade: 5.5 x 0.8 mm; with a partially insulated shaft; multicoloured



[Item No.: 210-769](#)
SCREWDRIVER; green