

5-Port 10/100/1000 Mbps Desktop Gigabit Ethernet Unmanaged Switch

MODEL NUMBER: NG5P



Energy-efficient unmanaged switch sets up in seconds with no configuration required. Provides a Gigabit network connection for multiple devices. Ideal for home or small offices, workgroups and creative production environments.

Description

The NG5P 5-Port 10/100/1000 Mbps Desktop Gigabit Ethernet Unmanaged Switch adds 10/100/1000 Mbps Ethernet capacity to your home office, small office, workgroup or creative production environment. Share large bandwidth-intensive files, such as CAD drawings and videos, at Gigabit speeds, improving efficiency and cutting costly downtime.

This desktop switch features five twisted-pair RJ45 Gigabit Ethernet ports that support auto-negotiable 10/100/1000 Mbps and auto MDI/MDIX cross-over detection functions for convenient plug-and-play capability. No configuration is required, so you can have your Gigabit network up and running immediately. Easy-to-read LEDs indicate connection and activity status for each port. IEEE 802.3x flow control allows smooth transmission of large files.

The NG5P supports IEEE 802.3az Energy Efficient Ethernet standards by putting unused ports into a low-power state without interrupting network connections. It consumes very little input power—just a single watt. The detachable five-foot input cord with NEMA 1-15P plug connects to a protected UPS, generator or mains input AC source.

Features

Unmanaged Network Switch for Home/Small Offices or Workgroups 5 twisted-pair RJ45 Gigabit Ethernet ports Auto-negotiable 10/100/1000 Mbps Automatic MDI/MDIX cross-over detection 10 Gbps switching capacity (2 Gbps per port with full duplex) Easy-to-read LEDs indicate connection and activity status for each port Supports 9k jumbo frames Supports MAC address auto-learning and auto-aging Supports 802.3x flow control (full duplex) and back pressure (half duplex)

Compliant with IEEE 802.3az Energy Efficient Ethernet Standards Automatically shifts unused ports to low-power state without interrupting network connection Consumes very little input power—just 1W Also meets IEEE 802.3ab, 802.3i, 802.3u and 802.3 standards

Durable Housing Fanless design for silent operation Detachable 5 ft. AC power cord with NEMA 1-15P plug Plug-and-play—no configuration necessary

Works with the Most Popular Web Browsers

The NG5P is browser-based and works independently from the connected computer's operating system. Because switch compatibility is based on common hardware standards, rather than system software dependencies, the NG5P accommodates most platforms. Preferred web browsers include Google Chrome (on both Windows and macOS) and Microsoft Edge (Windows only).

Highlights

- 5 auto-negotiable 10/100/1000 Mbps RJ45 ports
- Supports auto MDI/MDIX cross-over function
- Consumes very little input power—just 1W
- 2 Gbps switching capacity per port with full duplex
- Plug and play with no configuration required

Package Includes

- NG5P 5-Port 10/100/1000 Mbps Desktop Gigabit Ethernet Unmanaged Switch
- External power supply w/NEMA 1-15P plug and 5 ft. cord
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332194763
Product Type	Unmanaged Switch
INPUT	
Electrical Consumption (Max)	1W
Nominal Input Voltage Description	Included 5V DC output power adapter accepts 100-240V AC nominal input
Voltage Compatibility (VAC)	100-240
Input Plug Type	NEMA 1-15P
Input Cord Length (ft.)	5
Input Cord Length (m)	1.52
POWER	
Power Consumption (Watts)	1
CONNECTIONS	
Number of Ports	5
Ports	5
Ports Detail	5x 10/100/1000BASE-T
SFP Uplink Ports	0
PoE Supported Ports	0
Network Switch Ports	(5) 10/100/1000 (RJ45)
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Power LED (Green for Power On); One LED per RJ45 port (Green, LEDs flash to indicate port activity)
PHYSICAL	
Primary Form Factor	Desktop
Color	Black
Material of Construction	Plastic
Form Factors Supported	Desktop
Shipping Dimensions (hwd / in.)	3.10 x 3.00 x 5.20
Shipping Dimensions (hwd / cm)	7.87 x 7.62 x 13.21
Shipping Weight (lbs.)	0.40
Shipping Weight (kg)	0.18



Powering Business Worldwide

TRIPP-LITE
by **EAT•N**

Unit Dimensions (hwd / in.)	0.870 x 2.580 x 4.960
Unit Dimensions (hwd / cm)	2.2 x 12.6 x 6.6
Unit Weight (lbs.)	.19
Unit Weight (kg)	0.09
Rack Units	0
ENVIRONMENTAL	
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Relative Humidity	10 to 90% (non-condensing)
Operating Temperature	32 to 104 F (0 to 40 C)
COMMUNICATIONS	
Network Compatibility	1 Gbps (Gigabit)
Network Compatibility Details	Auto-negotiable
Switching Capacity	10 Gbps
Switching Capacity Details	2 Gbps per port with full duplex
FEATURES & SPECIFICATIONS	
Jumbo Frames	9000
Console Port	No
MAC Auto Learning	Yes
RMON	No
SNMP	No
Storm Control	No
DHCP Snooping	No
Auto MDI/MDIX Crossover Detection	Yes
Fans (Type/Quantity)	Fanless
STANDARDS & COMPLIANCE	
Product Certifications	EN 55022; EN 55024; EN 60950-1; NOM (Mexico)
Product Compliance	RoHS; IEEE 802.3 Auto-Negotiation; IEEE 802.3ab 1000Base-T; IEEE 802.3az (Energy Efficient Ethernet); IEEE 802.3i 10Base-T; IEEE 802.3u 100Base-TX/FX; IEEE 802.3x Flow Control; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide



1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.