


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	25AUG2023	NK	JDB
	D1	DRAWING RE-CREATED IN CREO	28DEC2023	NK	JDB








INSPECTION LEVEL 1: CONTROL CHART REQUIRED
① PROOF OF PROCESS CAPABILITY OR 100% TEST IF PROCESS CAPABILITY IS NOT ACHIEVED

INSPECTION LEVEL 2 AND 3: CONTROL CHART REQUIRED
② PROOF OF MEAN VALUE, STANDARD DEVIATION AND MACHINE CAPABILITY


③ PROOF OF VALUES OR PROOF OF ATTRIBUTIVE TEST

INFORMATION ON THE SCOPE OF TESTING AND DETECTION BY ERNI VA 7.3.2.3



TAPE ON REEL PACKAGING ACCORDING TO DIN IEC 60286-3
PACKAGING UNIT: 100 PCS



CONSIDER MOUNTING POSITION; PEG RIGHT



PCB-LAYOUT PROPOSAL



- DRAWING SPECIFICATION ACCORDING TO DOCUMENT 5_3_16-DOC-1806-00915
- COPLANARITY OF ALL CLIPS $\leq 0.1\text{MM}$

1	-	TAPE AND REEL	6
1	-	PAD	5
1	-	SOLDER CLIP LEFT	4
1	-	SOLDER CLIP RIGHT	3
12	-	PINS	2
1	-	HOUSING	1
484074-E	REV	DESCRIPTION	ITEM NO.
-		REV OF EACH ASSY NO. (WHEN BLANK, USE DWG. REV)	
QTY		PARTS LIST	

V=TURNED CONTACT (PCB SIDE CAN BE USED WITH POTTED COMPOUND)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN N. K. NIKHIL 04AUG2023	TE Connectivity			
		CHK M. SZELAG 07AUG2023				
		APVD J. DE BRUIJN 07AUG2023	NAME M12 FEMALE, A CODE, 12P, 17MM SMT V			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 2768-mK ISO 8015	PRODUCT SPEC 108-94887			
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH	APPLICATION SPEC 114-94781			
MATERIAL		-	WEIGHT -			
			CUSTOMER DRAWING			
			SCALE 5:1	SHEET 1 OF 1	REV D1	