

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT 2017 BY - TE CONNECTIVITY CORPORATION ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	INITIAL DRAWING	26NOV2016	VA	AT
	2	UPDATED TO REFLECT COMPONENT CHANGES	30AUG2017	RGV	AT
	A	REV PER ECR-18-012427	08AUG2018	MK	WS
	A1	ECR-18-018118	16NOV2018	WS	AT








SECTION J-J

1. BODY MATERIAL: (1.00) THICK COPPER ALLOY
2. NOTE REMOVED
3. BODY FINISH: SELECTIVE TIN PLATING OVER NICKEL IN GRIP AREA
4. BODY FINISH: SELECTIVE SILVER PLATING OVER NICKEL IN CONTACT AREA
5. SPRING (0.25) THICK COPPER ALLOY
6. WEEK (YWW) LASER MARKED 0.65 HIGH CHARACTERS,LOCATED APPROX AS SHOWN
7. NOTE REMOVED
8. SPRING FINISH: SELECTIVE TIN OVER NICKEL PLATING
9. SPRING FINISH: SELECTIVE SILVER OVER NICKEL PLATING











SCALE 3:1



SCALE 3:1



(H)	(G)	(F)	(E)	(B)	WIRE RANGE (mm²)	DESCRIPTION	PART NO	REV
2.35	9.60	9.45	2.00	9.00	10-16	LOOSE PIECE	1-2840575-2	
3.10	7.80	8.00	2.00	7.00	5-8	LOOSE PIECE	1-2840575-1	

1-2840575-2 SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.3
2 PLC ±0.10
3 PLC ±0.01
4 PLC ±0.0001
ANGLES ±-

MATERIAL - NOTED

FINISH - NOTED

DWN VISHWA A 26NOV2016
CHK A TYLER 26NOV2016
APVD W. SAMSAIR 08AUG2018
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT 7.18g

TE Connectivity

NAME RECEPTACLE ASSY, 180 DEG. PCON12
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2840575	-

CUSTOMER DRAWING | SCALE 4:1 | SHEET 1 OF 1 | REV A1

Downloaded from Arrow.com.