

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH – BASIC

CATALOG LISTING

V3-245

CK-C4500

CATALOG LISTING
V3-245
PAGE 1 OF 1

ISSUE
12

REPLACES



RELEASE NO.

CHECK

CHECK

REVISIONS

A	OBS	CO82209
	CSL	18 OCT 96
B	RE-INST	PR22527
	DCS	7 JAN 97




NOTE
1 – SWITCH MATERIALS WILL WITHSTAND TEMPERATURE OF 400°F FOR 100 HOURS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — — 10-25 OZ	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE — — — — 6 OZ MIN	L118 10A 1/8 HP 125 OR 250 VAC	ONE PLACE (.0)	±.030
DIFFERENTIAL TRAVEL — — — .006-.016		TWO PLACE (.00)	±.015
OVERTRAVEL — — — — .040 MIN		THREE PLACE (.000)	±.005
FREE POSITION — — — — .625 MAX		ANGLES	±
RELEASE TRAVEL — — — — .007 MIN	WEIGHT .017 LB		



DDM/CAD

DRAWN

CHECK

7 JAN 97

DCS