

Part Number : 878240007
Product Description : 1.27mm Signal Pitch, 0.80mm SCSI Pitch, 1.27mm Power Pitch SAS-2 Receptacle, Vertical, Surface Mount, with Straight Solder Tab, 1.60mm PCB Thickness, 29 Circuits, with Cap, Embossed Tape on Reel, Lead-Free
Series Number : 87824
Status : Obsolete
Product Category : I/O Connectors

Obsolete

Documents and Resources

Drawings

878240007_sd.pdf

PK-87824-001-001.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

EE-78012-002-001.pdf

EE-78164-001-001.pdf

EE-78695-002-001.pdf

EE-87824-001-001.pdf

EE-87824-002-001.pdf

EE-87824-003-001.pdf

SP-78012-002-001.zip

SP-78164-001-001.zip

SP-87824-003-001.zip

Specifications

PS-87824-029-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34

Downloaded from Arrow.com.

China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	I/O Connectors
Series	87824
Description	1.27mm Signal Pitch, 0.80mm SCSI Pitch, 1.27mm Power Pitch SAS-2 Receptacle, Vertical, Surface Mount, with Straight Solder Tab, 1.60mm PCB Thickness, 29 Circuits, with Cap, Embossed Tape on Reel, Lead-Free
Application	Board-to-Board
Comments	With Pick-and-Place Cap
Component Type	Receptacle
Product Name	SAS 6G,SAS-2

Obsolete

Downloaded from Arrow.com.

Type	N/A
UPC	822350717281

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.5A
Shielded	No
Voltage - Maximum	30V

Physical

Boot Color	N/A
Circuits Detail	Signal 14, Power 15
Circuits (Loaded)	29
Circuits (maximum)	29
Color - Resin	Black
Durability (mating cycles max)	500
Flammability	94V-0
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.778/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm

Obsolete

Downloaded from Arrow.com.

Pitch - Mating Interface	0.80mm, 1.27mm
Pitch - Termination Interface	0.80mm, 1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	0° to +55°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No
Wire Size (AWG)	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	SFF-8482 Hard Disk Drive and Backplane Plug

Obsolete

Downloaded from Arrow.com.