



**Part Number :** [1200270933](#)

**Product Description :** Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Pigtail, 0.25mm<sup>2</sup> PUR/PVC Cable, 10.0m (32.81') Length, PUR Cable Preferred Version in Europe

**Series Number :** 120027

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 403006P02M100

---

## Documents and Resources

### Drawings

[1200270933\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120027
Description	Nano-Change (M8) Single-Ended Cordset, 3 Poles, A-Coded, Male (Straight) to Pigtail, 0.25mm <sup>2</sup> PUR/PVC Cable, 10.0m (32.81') Length, PUR Cable Preferred Version in Europe
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	883906103767

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	60V

### Physical

Cable Diameter	4.32mm (.170")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy

Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	3
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A

---

This document was generated on Jun 10, 2026