



**C2G**  
**Discontinued - 2.5ft (0.76m) Cat6 Snagless Unshielded (UTP) Slim Ethernet Network Patch Cable - Blue**  
 Part No. 01075



The Cat6 Snagless Unshielded (UTP) Slim Network Patch Cable is the perfect solution for high density datacenter applications. The use of 28 AWG conductors allows for a 36% reduction in diameter over a standard Cat6 network patch cable. This reduced diameter provides a smaller cable surface area which allows for increased airflow when compared to standard Cat6 cables. The 28 AWG conductors also allow this cable to have a smaller bend radius than standard Cat6 cables. The small size and small bend radius of this cable allows it to be easily routed through cable management panels.

This cable is designed for fast Ethernet networks that require bandwidth-intensive voice, data, or video distribution applications. Constructed from high quality copper cable, this design minimizes Near-End Crosstalk (NEXT) levels. The molded, snagless boot prevents unwanted cable snags during installation and provides extra strain relief. Available in a variety of colors to easily color-code your network installation.

- This patch cable does not meet the recommend conductor size, 22-26AWG, requirement of ANSI/TIA-568-C.2. Attenuation is increased due to the smaller 28AWG conductors.

Maximum cable length recommendations:

- 96 Meter Channel (90 meters of horizontal cable and up to 6 meters of slim network patch cables)
- 93 Meter Channel (83 meters of horizontal cable and up to 10 meters of slim network patch cables)
- For POE/POE+ applications we limit bundles to 40 cables due to heat dissipation of these reduced diameter cables.

**Features & Benefits**

36% reduction in diameter compared to standard Cat5e cables	Snagless connector design
Meets the ANSI/TIA-568-C.2 standard for Patch Cord Performance	28AWG construction

**Specifications**

**General Info**

Product Line	C2G	Replaced by Part Number	01076
Color	Blue	UPC Number	757120010753
Country Of Origin	Vietnam	Features	PoE (Power Over Ethernet)
Connector Hood Material	PVC	Application Sector	Commercial, Industrial, Residential
Type	Cable		

**Dimensions**

Product Length US	2.5 FT	Cable Length	2.5 ft
Outside Diameter	3.8 mm		

**Listing Agencies / 3rd Party Agencies**

CE Certified	Yes	REACH Compliant	Yes
--------------	-----	-----------------	-----

**Additional Information**

RoHS Compliant	Yes
----------------	-----

---

## Technical Information

---

Jacket Material	PVC (Polyvinyl Chloride)	Category Performance Application	Cat6
Wiring Scheme	T568B	Wire Gauge	28 AWG
Shielded/Unshielded Cable	Unshielded	Conductor	4-Pair Twisted
Shield Type	UTP	Cable Type	Ethernet Patch Cable
Jacket Rating	Standard / Non-Rated	Cable Diameter	3.8 mm
Connector Type	Booted, Slim, Snagless	Indoor/Outdoor	Indoor
Connector 2	RJ-45 Male	Connector 1	RJ-45 Male
Bandwidth	500 MHz	Storage Temperature	-20° - 80° C

---