



REV.	DATE	ECR NO.	DESCRIPTION
NC	04/30/00	—	INITIAL RELEASE
A	11/22/08	—	UPDATE DRAWING FORMAT



RECOMMENDED CABLE
STRIPPING DIM'S

NOTES:

1. CRIMPED FERRULE HEX CRIMP SIZE.213" [5.41]

				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
8					DRAWN	GRS	11/22/08									
7					CHECKED				PART DESCRIPTION MINI–UHF R/A CRIMP PLUG (FOR RG–58/U, 58C/U CABLE)							
6					ISSUED											
5	FERRULE	COPPER	NICKEL		1	SHEET	1	OF	1	PART NO. 182323						
4	COVER	BRASS	NICKEL		1	CAD FILE			C:/182/182323.DWG						DWG. NO. 182323.DWG	
3	CONTACT PIN	BRASS	GOLD		1											
2	INSULATOR	PTFE	NATURAL	1												
1	BODY	BRASS	NICKEL	1												
DESCRIPTION				MATERIAL	FINISH	QTY										