




PRODUCT NUMBER: 0280-2-17-01-06-27-02-0

www.mill-max.com  
DATA SHEET



## 0280-2-17-01-06-27-02-0 SPECIFICATIONS



General Info		Materials	Technical Specs
Description <sup>1</sup> :	Receptacle With A Wire Wrap Tail	Shell Material <sup>3</sup> :	Mechanical life 1,000 Cycles Minimum (Durability) <sup>6</sup> :
Mounting Feature:	Press-Fit into a Non-Plated Through Hole (NPTH)	Shell Plating <sup>4</sup> :	Operating Temperature -55/+125° C Range <sup>7</sup> :
Mounting Hole:	.081" (2,057mm)	Contact Plating <sup>5</sup> :	Maximum Current 16A @ 30° C Temp. Rise
Pin Diameter Range:	.022"-.032" (0,559-0,813mm)		Maximum Derated Current 12.8A
Packaging:	Packaged in Bulk		Contact Resistance: 10 mΩ Max
RoHS:	No		Shock <sup>8</sup> : No Elect. Discontinuity > 1μs @ 50g
Product Lifecycle <sup>2</sup> :	Active		Vibration <sup>9</sup> : No Elect. Discontinuity > 1μs @ 10-2000HZ, 20 G
Country Of Origin:	USA		

## NOTES:

1. Standard Tolerances:  
Lengths +/- .005" (0,13)  
Diameters: +/- .002" (0,051)  
Angles: +/- 2°
2. Part is Active and in Production, No Scheduled Obsolescence
3. Brass Alloy 360 per ASTM B 16, or 385 per ASTM B455
4. TIN/LEAD (93/7) per ASTM B 545 (Appendix X6.3.2.5 to eliminate whisker growth) Bright finish; NICKEL per ASTM B 689, Type 2 (Bright)
5. GOLD per ASTM B 488, Type 1 (99.7% min. gold), Code C (130-200 HK {Knoop hardness}), NICKEL per ASTM B 689, Type 2 (Bright)
6. Receptacles are capable of 1,000 Minimum insertion/extraction cycles for a broad range of applications. Mating pin size, shape and finish, along with application specific variables, will affect the life of a receptacle contact.
7. Per IEC 60512-11-(4,-9,-10,-12)
8. Per IEC 60512-6-3: Test 6c: Shock
9. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

## CONTACT:

### #06 CONTACT FOR .022"-.032" DIAMETER PINS ( $\delta = .007$ ) 4-FINGER (BeCu), GROUP D



The insertion / extraction force characteristics above were derived using a 30 microinch gold-plated contact and polished steel gauge pins having a bullet-shaped tip.

The curves represent typical average values; they are best used to compare the differences between similar size contacts and to guide you in selecting one that is suitable for your application. Your results may vary, so for your specification, we encourage you to obtain complimentary samples for your evaluation.

Material	Beryllium Copper	Fingers	4
Compliance ( $\delta$ )	0.007	Length	.113" (2,870mm)
Maximum Current	16A @ 30° C Temp. Rise	Maximum Operating Temp @ Max Current	120.00° C
20% De-rated Maximum Current	12.80A	Contact Resistance	10.00mΩ Max
Contact Group	D		

## ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance , Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

## RELATED LINKS AND DOCUMENTS

Engineering Notebook: ( <https://www.mill-max.com/engineering-notebooks/pin-receptacles/the-backbone-of-your-interconnect-system> )

Environmental Compliance: ( <https://www.mill-max.com/rohs> )