

Johanson Part Number VPCT501W102K1GV001T

Johanson Part Number: VPCT501W102K1GV001T

Johanson Company: JDI

Legacy P/N: 501R15W102KV4T

Size for Capacitors (EIA): 0805

Description: Capacitors High Voltage PME SMD > 200V, 0805, X7R, 500.00V, 1,000.00pF±10% cap, Ni/Sn (RoHS) cap, 7" Reel Paper Tape cap

Specification Number: None

Life Cycle Stage: Active

NCNR: No

AEC Q200 Qualified: No

Thickness (Max): 0.050

Schedule B: 8532.24.00.20

Thickness (Min): None

ITAR: No

End Band(Min): 0.01

ECCN: EAR99

End Band (max): 0.030

RoHS Compliance: Yes, RoHS 10/10

Standard Item: No

REACH: Yes

Lead Time Typical (Weeks)*: 16

Country of Origin: US, MX, TW, or CN

Length (Min): 0.070

Product Family: Capacitors

Length (Max): 0.090

Product Subfamily: Capacitors High Voltage SMD ≥ 500V

Width (Min):0.040

Capacitance Value: 1000.000

Width (Max): 0.060

Cap Unit of Meas: pF

Part Weight (mg): 24.00

Tolerance: ±10%

Packaged Width (lb) Arm: None

Voltage: 500.0

Packaging: 7" Reel Paper Tape

Dielectric Temp Coefficient: X7R

Packaging Qty: 3000

Termination: 68

Operating Temp Range: -55°C to +125°C

Marking: No Mark

Storage Temp Range (Packaged): +5°C to +40°C with RH 20% to 70%

Product Release Date: Jan. 3, 2006

Storage Temp Range (None Operating): -65°C to +125°C

Harmonization: 8532.24.00.20

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: <https://www.johansondielectrics.com/surface-mount-mlc-capacitors>

Printed from: <https://www.johansontechnology.com/part/VPCT501W102K1GV001T/>