


SIGN	DATE	DESCRIPTION	APPROVER
△	01/20'07	The Soldering temperature from 245° to 250°	Aaron
△	10/29'08	ADD Tolerance	Seamus
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Terminal body (Contact pin): Brass
- Wire guard: Stainless steel
- Surface of solder tail: Tin plated
- Insulator (housing): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 150VAC
- Current rating: 2A
- Wire range:
- Solid wire(AWG): 20-26
- Stranded wire(AWG): 20-26
- Pull force:
- Screw:
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec △
- Safety Approval: 

HA xx 51 x 0 xxxx G

02	2 CONTACTS	2	Red	0000 Standard @ Logo
03	3 CONTACTS	3	Orange	000A Standard ANY Logo
...	...	5	Green(RAL6018/T)	Any special item by customer request, please contact sales department.
24	24 CONTACTS	8	Grey(RAL7004/P)	

G: Pb<40,000ppm

Dimension

DIM A	(N+1)×2.54
DIM B	(N-1)×2.54


N=Number of poles △




POLES	DIM A	DIM B
2p-8p	±0.15	±0.15
9p-12p	±0.25	±0.25
13p-18p	±0.30	±0.30
19p-24p	±0.40	±0.40

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	HA-2.54mm 180° Series						
PART NO.	HAxx51x0xxxxG			DWG NO.	8HA0502		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
	Seamus 2008.10.29	Seamus 2008.10.29	Aaron 2007.01.20		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
						X.XX	±0.10
				SHEET: 01/01	REV.: E	X°	±1°



P.C.B. LAYOUT