

Catalog No. TY25MFR

Description: CABLE TIE 50LB 7IN WHI NYL FLM RTD

UPC No 786210899466

Home > Wire & Cable Management > Ty-Rap > Cable ties

Cable Tie, Flame Retardant White Nylon 6.6, Temperature Range of -20 to 65 Degrees Celsius (-4 to 149 F) for Indoor Applications, Length of 185mm (7.3 Inches), Width of 4.6mm (0.18 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 48mm (1.89 Inches), Tensile Strength Rating of 220 Newtons (49 Pounds)

Representative Image

Descriptors

Category	Cable ties
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.

Specifications

Material	Nylon/Polyamide 6.6
Color	White
Lock Mechanism	Stainless Steel Barb
Tensile Strength	49 pounds , 220 newtons

Classifications

Brand Name	Ty-Rap
Standard	UL E49405 UL E49405

Dimensions

Width	0.18 in , 4.6 mm
Length	7.3 in , 185 mm
Thickness	0.05 in , 1.3 mm
Bundle Diameter	0.12 to 1.89 in , 3.0 to 48 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	4.6 mm
Length belt/tape/tie	185 mm
Length belt/tape/tie	7.3 inch
Tie thickness	1.3 mm
Tie thickness	0.05 inch
Max. bundle diameter	48 mm
Min. holding force	220 N
Operation temperature	-60-+65 °C
Operation temperature	-4-+149 °F
Model	Internal toothing
Band closure	Steel nose
Material	Plastic
Material quality	Polyamide flame retardant
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y
Colour	White
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
VG approval	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V0