

Industrial Power Supplies

TIB 240 Series, 240 Watt

- Slim profile, for DIN-rail mounting
- Alternative side-mounting for flat panels
- High power factor by active power correction
- Very high efficiency up to 95%
- Back power immunity
- 150% peak current for 4 sec.
- Operating temperature range: -40°C to +70°C max.
- Adjustable output voltage
- DC-OK indicator
- Short circuit and overload protection



Other output power of same series:
www.tracopower.com/overview/tib



This generation of DIN-rail power supplies combines the most efficient circuit topology with optimized cost/performance ratio for industrial environments and for electrical control cabinets.

They have a very high efficiency of up to 95.0% which allows a very slim package design. The output voltage is adjustable from -2% to +17%. The case offers the potentially useful feature to fix the DIN-rail clip to the side wall for the mounting inside flat panels. Over a period of minimum 4 seconds they can operate with a boost power of 150%. The boost power facilitates the activation of stepper motors, solenoids or actuators. The units operate with a high power factor of up to 98% by active power factor correction which also keeps the input inrush current low. The TIB series are also available with other nominal power of 80, 120 or 480 Watt (+50% boost power). They come with the safety standard approvals for IEC/EN 60950-1, UL 60950-1 and UL 508.

Models

Order Code	Output Power (max.)	Output Voltage nom. (adjustable)	Output Current (max.)	Efficiency (typ.)
TIB 240-124	240 W	24 VDC (23.5–28.0)	10 A	95.0 %
TIB 240-148	240 W	48 VDC (47.0–56.0)	5 A	95.0 %

Input Specifications

Input voltage	– nominal ranges – effective ranges	100 – 240 VAC 85 – 264 VAC (below 90 VAC a derating of 3%/V is required)
Input voltage frequency		45 – 65 Hz
Standby power consumption		2.3/2.3 W (115/230 VAC)
Power Factor Correction (PFC)		0.98/0.92 (115/230 VAC)
Harmonic limits	– acc. EN 61000-3-2	class A, D
Inrush current		15/30 A max. (115/230 VAC)

Output Specifications

Output voltage adjustment ¹⁾		24 Vout models: 23.5 – 28.0 V 48 Vout models: 47.0 – 56.0 V
Regulation	– Input variation – Load variation (10–90 %)	0.1 % max. 0.5 % max.
Temperature coefficient		0.02 %/K
Hold-up time		20 ms min.
Start-up time		2 s max.
Ripple and Noise (20MHz bandwidth)	24 Vout models: 48 Vout models:	100 mVp-p max. 200 mVp-p max.
Output overvoltage protection (OVP) ²⁾	24 Vout models: 48 Vout models:	32 – 35 V 56 – 60 V
Power back immunity ³⁾		< OVP level
Operation	– Nominal operation – Peak power operation – Constant current (cc)	100 % of Iout nom. 105 – 150 % of Iout nom. > 155 % of Iout nom.
Duty cycle ⁴⁾ (for peak and cc mode)	– Threshold – CC or peak operation timer – normal operation / off period	> 105 % 4 s max. (switch off) 10 s typ. (automatic restart after switch off or peak and cc operation timer reset)
Short circuit		Switch off after 4s delay, automatic restart
DC OK signal	– Threshold for Vout – DC ON – DC OFF	24 Vout models: on: > 22.5 V typ., off: < 21.5 V typ. 48 Vout models: on: > 45 V typ., off: < 43 V typ. relay contact closed, 1 A max., < 100 mOhm (also indicated by green LEDs: front and side) relay contact open, 30 V max.

¹⁾ Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

²⁾ In case of an internal error a second voltage regulation loop keeps the output voltage at a safe level, the power supply turns off and restarts after typ. 10 seconds.


³⁾ When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if external voltage is applied continuously.

⁴⁾ In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every typ. 10 seconds.


General Specifications

Operating temperature range	–40°C to +70°C max.
Derating	2 %/K above +60°C
Cooling	convection cooling, no internal fan
Overtemperature protection	switch off at overtemperature
Humidity (non condensing)	5–95 % rel. H max.
Altitude during operation	2000 m max.
Isolation Voltage	– Input/Output 4250 VDC – Input/Chassis 1500 VDC – Output/Chassis 750 VDC
Creepage Clearance	– Input/Output 8 mm – Input/Chassis 4 mm – Output/Chassis 1.5 mm
MTBF (acc. to IEC 61709 at 25°C)	> 1'300'000 h
Safety standards	– Information technology equipment IEC/EN 60950-1, UL 60950-1 – Safety low voltage switchgear and controlgear CSA 22.2 No 60950-1-03 – Certification documents UL 508 www.tracopower.com/overview/tib
Electromagnetic compatibility (EMC), Emissions	EN 61000-6-3, EN 61204-3 – Conducted emission input EN 55032, EN 55011 class B – Radiated RI emission EN 55032, EN 55011 class B
Electromagnetic compatibility (EMC), Immunity	EN 61000-6-2, EN 61204-3 EN 50121-4 EN 50121-3-2 – Railway applications signalling apparatus IEC/EN 61000-4-2 4 kV/8 kV criteria A – Railway applications rolling stock apparatus IEC/EN 61000-4-3 10 V/m criteria A – Electrostatic discharge (ESD) IEC/EN 61000-4-4 2 kV criteria B – Radiated RF field immunity IEC/EN 61000-4-5 1 kV/2 kV criteria B – Electrical fast transient / burst immunity IEC/EN 61000-4-6 10 V criteria A – Surge immunity IEC/EN 61000-4-8 30 A/m criteria A – Immunity to conducted RF disturbances IEC/EN 61000-4-11 criteria B/C – Power frequency field immunity SEMI F47 (230 VAC) criteria A – Mains voltage dips and interruptions – Voltage sag immunity
Environment	– Railway applications shock and vibration according EN 61373 – Vibration acc. IEC 60068-2-6-3 3 axis, 2 g sine sweep, 10–55 Hz, 11 okt/min – Shock acc. IEC 60068-2-27 3 axis, 25 g half sine, 11 ms
Enclosure material	– Chassis aluminium – Cover stainless steel
Mounting	– DIN-rail mounting for DIN-rails as per EN 50022-35×15/7.5
Environmental compliance	– Reach www.tracopower.com/info/reach-declaration.pdf – RoHS RoHS directive 2011/65/EU
Connection	screw terminals

Function Specification




Output Characteristic




Characteristic: Output voltage vs output current for overload conditions until switch off after 4s at nominal input voltages

Output Characteristic (continued)




Derating: max load vs input voltage



Derating: Load vs ambient temperature

Outline Dimensions



Alternative side mounting:

