

Terminal Part Number: 10890230

Surface Plating: SN

Material Thickness [mm]: -

Cross Section [mm²]: 0,50 | 0,80

This document is non-contractual
and for information only.

For more information, please
consult your local sales office

Cable Type codes: 1005

Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY

Insulation Range Φ[mm]: 1,60 - 2,20

Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
1005 0,50		1,74	80	1,20	0,05	2,05	0,10	2,20	0,10	2,70	0,10
1005 0,80		2,03	90	1,30	0,05	2,05	0,10	2,30	0,10	2,70	0,10

Cable type code legend:

1005:



Industry Designator: SAE

Conductor Material: COPPER

Conductor Plating: NONE

Insul. Material: PVC, PVDF, XLPE

Insul. Wall Designator: THIN



Crimp Information Sheet

DELPHI

Terminal Part Number: 10890230
 Surface Plating: SN
 Material Thickness [mm]: -
 Cross Section [mm²]: 0,35 | 0,50 | 0,75 | 1,00

*This document is non-contractual
 and for information only.*



*For more information, please
 consult your local sales office*

Cable Type codes: 2010
 Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
 Insulation Range Φ [mm]: 1,20 - 2,10
 Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
2010 0,35		1,34	75	1,15	0,05	2,25	0,10	2,10	0,10	2,70	0,10
2010 0,50		1,50	75	1,15	0,05	2,25	0,10	2,10	0,10	2,70	0,10
2010 0,75		1,75	120	1,40	0,05	2,10	0,10	2,20	0,10	2,65	0,10
2010 1,00		1,95	160	1,50	0,05	2,15	0,10	2,30	0,10	2,70	0,10

Cable type code legend:

2010: ACW0219, FIAT T2 FLRY, FL RENAULT R1, FL RENAULT R3, FLR
 (AGP0219), FLR2X-A, FLR4Y-A, FLR9Y, FLRX-B, FLRY-A, FLRYB, FLRY-B
 Industry Designator: DIN
 Conductor Material: COPPER
 Conductor Plating: NONE
 Insul. Material: PA, POLYOLEFIN, PP, PVC, SYNTHRESIN, XLCOPOLY, XLPBT, XLPE,
 XLPE/PVDF, XLPVC
 Insul. Wall Designator: THIN



Terminal Part Number: 10890230
Surface Plating: SN
Material Thickness [mm]: -
Cross Section [mm²]: 0,50

*This document is non-contractual
and for information only.*

*For more information, please
consult your local sales office*

Cable Type codes: 3004
Crimp Process: (C) CRIMP ONLY - TERMINAL IS APPLIED CRIMP ONLY
Insulation Range Φ[mm]: 1,50 - 1,70
Seal(s): NONE

Cable type / seal	Arrangement	Nominal Insul. diam [mm]	Tear-out force [N]	CCH [mm]	Tol CCH [mm]	CCW [mm]	Tol CCW [mm]	ICH [mm]	Tol ICH [mm]	ICW [mm]	Tol ICW [mm]
3004 0,50		1,60	80	1,15	0,05	2,25	0,10	2,10	0,10	2,70	0,10

Cable type code legend:

3004: AVSS
Industry Designator: JIS/JA
Conductor Material: COPPER
Conductor Plating: NONE
Insul. Material: PVC, XLPE, X-PVC
Insul. Wall Designator: THIN

