

Memory Module Specifications

KSM26RS4/16MRR

16GB 1Rx4 2G x 72-Bit PC4-2666

CL19 Registered w/Parity 288-Pin DIMM

DESCRIPTION

Kingston's KSM26RS4/16MRR is a 2G x 72-bit (16GB) DDR4-2666 CL19 SDRAM (Synchronous DRAM) registered w/ parity, 1Rx4, ECC, memory module, based on eighteen 2G x 4-bit FBGA components. The SPD is programmed to JEDEC standard latency DDR4-2666 timing of 19-19-19 at 1.2V. Each 288-pin DIMM uses gold contact fingers. The electrical and mechanical specifications are as follows:

FEATURES

- Power Supply: VDD = 1.2V
- VDDQ = 1.2V
- VPP = 2.5V
- VDDSPD = 2.41V to 2.75V
- Functionality and operations comply with the DDR4 SDRAM datasheet
- 16 internal banks
- Bank Grouping is applied, and CAS to CAS latency (tCCD_L, tCCD_S) for the banks in the same or different bank group accesses are available
- Data transfer rates: PC4-2666, PC4-2400, PC4-2133, PC4-1866, PC4-1600
- Bi-Directional Differential Data Strobe
- 8 bit pre-fetch
- Burst Length (BL) switch on-the-fly BL8 or BC4(Burst Chop)
- Supports ECC error correction and detection
- On-Die Termination (ODT)
- Temperature sensor with integrated SPD
- This product is in compliance with the RoHS directive.
- Per DRAM Addressability is supported
- Internal Vref DQ level generation is available
- Write CRC is supported at all speed grades
- CA parity (Command/Address Parity) mode is supported

SPECIFICATIONS

CL(IDD)	19 cycles
Row Cycle Time (tRCmin)	46.25ns(min.)
Refresh to Active/Refresh Command Time (tRFCmin)	350ns(min.)
Row Active Time (tRASmin)	32ns(min.)
Maximum Operating Power	*
UL Rating	94 V - 0
Operating Temperature	0° C to +85° C
Storage Temperature	-55° C to +100° C

*See IDD Specifications (page 2)

Module Assembly

DRAM: MICRON (R-DIE)



RCD: Rambus

Continued >>

IDD Specifications

Symbol	2666	Units
I_{DD0}	756	mA
I_{PP0}	72	mA
I_{DD1}	846	mA
I_{DD2N}	648	mA
I_{DD2NT}	666	mA
I_{DD2P}	540	mA
I_{DD2Q}	612	mA
I_{DD3N}	684	mA
I_{PP3N}	54	mA
I_{DD3P}	540	mA
I_{DD4R}	1584	mA
I_{DD4W}	1260	mA
I_{DD5R}	810	mA
I_{PP5R}	90	mA
I_{DD6N}	576	mA
I_{DD6E}	936	mA
I_{DD6R}	342	mA
I_{DD6A}	144	mA
I_{DD6A}	342	mA
I_{DD6A}	522	mA
I_{DD6A}	936	mA
I_{PP6X}	90	mA
I_{DD7}	3348	mA
I_{PP7}	234	mA
I_{DD8}	432	mA

MODULE DIMENSIONS



The product images shown are for illustration purposes only and may not be an exact representation of the product.
Kingston reserves the right to change any information at anytime without notice.