



Data Sheet | Item Number: 294-5005

Lighting connector; push-button, external; without ground contact; 5-pole; Lighting side: for solid conductors; Inst. side: for all conductor types; max. 2.5 mm²; Surrounding air temperature: max 85°C (T85); white

<https://www.wago.com/294-5005>



Color: white



Dimensions in mm

Field-wiring terminal block, 294 Series, with 10 mm pin spacing

Quick and easy connections are guaranteed with this field-wiring terminal block (item number 294-5005). Ensure that the strip lengths are between 8 mm and 9 mm when connecting conductors to this field-wiring terminal block. This product features four conductor terminals and utilizes Push-in CAGE CLAMP® as well as PUSH WIRE®. Push-in CAGE CLAMP® technology provides a universal connection solution for all conductor types. It allows both solid and fine-stranded conductors with ferrules to be inserted directly into the clamping point without the need for tools. Our PUSH WIRE® connection is the simple and reliable method for connecting solid conductors. Dimensions: 50 x 21.53 x 27.3 mm (width x height x depth). Depending on the conductor type, this field-wiring terminal block is suitable for conductor cross sections ranging from 0.5 mm² to 2.5 mm² on one side and for conductor cross sections from 0.5 mm² to 2.5 mm² on the other side as well as conductor cross sections from 0.5 mm² to 1.5 mm² and from 0.5 mm² to 0.75 mm². You can connect five potentials / five poles using the twenty-five clamping points. The clamping spring is made of chrome-nickel spring steel (CrNi), the contacts are made of electrolytic copper (ECu), and the white housing is made of polycarbonate (PC) for insulation. Tin is used for coating the contact surfaces.

Electrical data					
Ratings per		IEC/EN 60998-1		Ratings per IEC/EN – Notes	
Overvoltage category	III	III	II	Ratings (note)	Connection points
Pollution degree	3	2	2		
Nominal voltage	-	-	500 V		
Rated surge voltage	-	-	4 kV		
Rated current	-	-	24 A		



Ratings per	IEC/EN 60998-2-2		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Nominal voltage	-	-	500 V
Rated surge voltage	-	-	4 kV
Rated current	-	-	24 A

Connection data

Clamping units	25
Total number of potentials	5
Number of connection types	4
PE function	without PE contact

Connection 1

Connection type	External 1
Connection technology	Push-in CAGE CLAMP®
Number of connection points	2
Actuation type	Push-button
Connectable conductor materials	Copper
Solid conductor	0.5 ... 2.5 mm² / 18 ... 12 AWG
Solid conductor; push-in termination	0.5 ... 2.5 mm² / 18 ... 12 AWG
Stranded conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with ferrule; push-in termination	0.5 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches
Pole number	5
Wiring direction	Side-entry wiring

Connection 2

Connection type	Internal 2
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 2.5 mm² / 18 ... 14 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 1 mm² / 18 ... 16 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1.5 mm² / 18 ... 14 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 3

Connection type	Internal 3
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 1.5 mm² / 18 ... 16 AWG
Fine-stranded conductor; with insulated ferrule	0.5 ... 0.75 mm² / 18 AWG
Fine-stranded conductor; with uninsulated ferrule	0.5 ... 1 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches

Connection 4

Connection type	Internal 4
Connection technology	PUSH WIRE®
Number of connection points	1
Actuation type	Push-in
Solid conductor	0.5 ... 0.75 mm² / 18 AWG
Strip length	8 ... 9 mm / 0.31 ... 0.35 inches



Physical data	
Pin spacing	10 mm / 0.394 inches
Width	50 mm / 1.969 inches
Height	21.53 mm / 0.848 inches
Height from the surface	17 mm / 0.669 inches
Depth	27.3 mm / 1.075 inches

Mechanical data	
Marking	plain
Mounting type	Snap-in foot

Material data	
Note (material data)	<a href="#">Information on material specifications can be found here</a>
Color	white
Material group	IIIa
Insulation material (main housing)	Polycarbonate (PC)
Flammability class per UL94	V0
Clamping spring material	Chrome-nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact Plating	Tin
Fire load	0.302 MJ
Halogen-free	Yes
Weight	15.2 g


Environmental requirements	
Temperature stability	120 °C
T marking	T85


Commercial data	
Product Group	8 (Misc. Chassis Mount Blocks)
PU (SPU)	250 pcs
Packaging type	Foil
Country of origin	CH
GTIN	4050821098157
Customs tariff number	85369010000



Product classification	
UNSPSC	39121409
eCl@ss 10.0	27-14-11-06
eCl@ss 9.0	27-14-11-06
ETIM 9.0	EC001284
ETIM 8.0	EC001284
ECCN	NO US CLASSIFICATION



Environmental Product Compliance	
REACH Candidate List Substance	Perfluorobutane sulfonic acid (PFBS) and its salts
RoHS Compliance Status	Compliant,No Exemption
SCIP notification number (Austria)	58ff7fda-f6a4-44da-bebb-e9fb0c87772c
SCIP notification number (Belgium)	04f971b1-a3c8-419b-b59c-3c77fc975977
SCIP notification number (Bulgaria)	9f941214-774f-4ece-9211-1484165244d6
SCIP notification number (Czech Republic)	ec269270-b7f0-4d5b-bfaf-27a7f86f649a
SCIP notification number (Denmark)	864fd9eb-622c-4daa-bad4-5679029f524b
SCIP notification number (Finland)	cd81d19d-5f06-4486-a08c-2094af24b9ce
SCIP notification number (France)	bf83d60b-2cae-4558-b83d-4c8d50fece6f
SCIP notification number (Germany)	a131fd55-6ec0-4629-bee4-f8543b64161b
SCIP notification number (Hungary)	8d0076e0-b511-435e-bd7e-aa7738d058ec
SCIP notification number (Italy)	d6771206-76c7-4d1f-b6e6-940228753d83
SCIP notification number (Netherlands)	220615a9-70fc-4a4c-83e7-81a8f052dfd1
SCIP notification number (Poland)	fc25ef8e-8ad8-4009-b834-1082347d1176
SCIP notification number (Romania)	df5a78dc-e539-46a0-9fa1-097380cd4682
SCIP notification number (Sweden)	5e3922cc-e640-4cf2-97de-3bb70932f447

Approvals / Certificates											
General approvals		Declarations of conformity and manufacturer's declarations									
											
Approval	Standard	Certificate Name									
ENEC 05 DEKRA Certification B.V.	EN 60998	2128791.01									
		<table><tr><th>Approval</th><th>Standard</th><th>Certificate Name</th></tr><tr><td>EU-Declaration of Confor- mity WAGO GmbH &amp; Co. KG</td><td>-</td><td>-</td></tr><tr><td>UK-Declaration of Confor- mity WAGO GmbH &amp; Co. KG</td><td>-</td><td>-</td></tr></table>	Approval	Standard	Certificate Name	EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-	UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-
Approval	Standard	Certificate Name									
EU-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-									
UK-Declaration of Confor- mity WAGO GmbH & Co. KG	-	-									

Downloads	
Environmental Product Compliance	
Compliance Search	
Environmental Product Compliance 294-5005	

Documentation			
Bid Text			
294-5005	19.02.2019	xml 5.57 KB	
294-5005	13.06.2017	doc 28.00 KB	



CAD/CAE-Data

CAD data	CAE data
2D/3D Models 294-5005	WSCAD Universe 294-5005
	ZUKEN Portal 294-5005

1 Compatible Products

1.1 Optional Accessories

1.1.1 Strain relief

1.1.1.1 Strain relief



**Item No.: 294-370**  
Strain relief; for 294 Series; with snap-in mounting feet; white



**Item No.: 294-375**  
Strain relief; for 294 Series; without snap-in mounting feet; white

1.1.1.2 Strain relief plate



**Item No.: 294-364**  
Strain relief plate; for 294 Series; for multi-core cables; 3- to 5-pole; with secured clamp; white



**Item No.: 294-384**  
Strain relief plate; for 294 Series; for single strands; 3- to 5-pole; with secured clamp; white

1.1.2 Tool


1.1.2.2 Operating tool




**Item No.: 206-294**  
Disconnection tool; green

Installation Notes


Installation



5-pole – without ground contact




Snap-in foot



Drilled hole for snap-in mounting foot





Conductor termination





EUROPE
1 x 0.5 ... 2.5 mm <sup>2</sup> "s"
1 x 0.5 ... 1.5 mm <sup>2</sup> "s"
1 x 0.5 ... 0.75 mm <sup>2</sup> "s"
AMERICA
1 x AWG 18 ... 14 "s"
1 x AWG 18 ... 16 "s"
1 x AWG 18 "s"
JAPAN
1 x 0.8 ... 1.6 mm diam. "s"
1 x 0.8 ... 1 mm diam. "s"
1 x 0.8 mm diam. "s"

EUROPE
2 x 0.5 ... 2.5 mm <sup>2</sup> "s, str, f-str"
AMERICA
2 x AWG 18 ... 12 "s"
2 x AWG 18 ... 14 "s, f-str"
JAPAN
2 x 0.8 ... 2 mm diam. "s"
2 x 0.5 ... 2 mm <sup>2</sup> "str, f-str"



**Internal connection:**  
PUSH WIRE® for internal wiring with solid conductors

**External connection:**  
Push-in CAGE CLAMP® for field-wiring with all conductor types



Terminating five conductors per pole – solid and fine-stranded.

