


| 6    |            | 5                                      |  | 4   |     | 3 |  | 2    |    | 1                                 |       |
|------|------------|----------------------------------------|--|-----|-----|---|--|------|----|-----------------------------------|-------|
| ITEM | PART#      | DESCRIPTION                            |  | QTY | UOM |   |  | FROM | TO | DESCRIPTION                       | COLOR |
| A    | 5601230200 | DuraClik ISL housing 2p                |  | 1   | PC  |   |  | A1   | -- | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| B    | 5601250200 | DURACLIK ISL RETAINER 2P               |  | 1   | PC  |   |  | A2   | -- | 1X0.35 SQMM PVC BARE CU BK FLRY-A | BLACK |
| C    | 5601240101 | DURACLIK ISL crimp receptacle terminal |  | 2   | PC  |   |  |      |    |                                   |       |
| D    | --         | PAPER PRINTED PAPER WHITE              |  | 1   | PC  |   |  |      |    |                                   |       |



| TABLE       |        |          |                                      |
|-------------|--------|----------|--------------------------------------|
| PART NUMBER | L1     | L2 (REF) | TITLE                                |
| 2183231021  | 150±8  | 63       | DURA-CLIK ISL R-S 2CKT 150MM DISC Sn |
| 2183231022  | 300±10 | 138      | DURA-CLIK ISL R-S 2CKT 300MM DISC Sn |
| 2183231023  | 600±10 | 288      | DURA-CLIK ISL R-S 2CKT 600MM DISC Sn |

- NOTES
- Free ends must be stripped, twisted & tinned. The length of tinning is 5±1mm. Tinning dia must be 1mm Max.
  - Connector view shown is from mating side.
  - Label text must be 2mm max. in height with Arial font.
  - Label must be wrapped in Flag type on a single cable.

MOLEX P/N  
MOLEX  
BATCH WK/YR  
DETAIL A

| REVISION   |     |                 |         |
|------------|-----|-----------------|---------|
| DATE       | REV | DESCRIPTION     | CHANGER |
| 24/05/2021 | A   | INITIAL RELEASE | ARAJU   |

FUNCTIONAL SYMBOLS

$\frac{F}{A} = 0$

$\frac{F}{E} = 0$

$\frac{F}{P} = 0$

DIVISIONAL SYMBOLS

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

DIMENSION UNITS

mm

SCALE

NTS

CURRENT REV DESC:

EC NO: 665457

DRWN: ARAJU

CHK'D: RDESAI01

APPR: RDESAI01

INITIAL REVISION:

DRWN: ARAJU

APPR: RDESAI01

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

GENERAL TOLERANCES (UNLESS SPECIFIED)

ANGULAR TOL ± °

4 PLACES ±

3 PLACES ±

2 PLACES ±

1 PLACE ±

0 PLACES ±

THIRD ANGLE PROJECTION

DRAWING

SERIES

MATERIAL NUMBER

CUSTOMER

SHEET NUMBER

2021/05/22

2021/05/28

2021/05/28

2021/05/22

2021/05/28

2183231021

PSD

000

A

1 OF 1

mo

le

x

SEE TABLE

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER

DOC TYPE

DOC PART

REVISION