

NTE30140 thru NTE30145 Discrete LED Indicators 3mm (T-1) Package Type

Features:

- All 3mm Types w/Water Clear Lens:
 - NTE30140 (Red)
 - NTE30141 (Green)
 - NTE30142 (Blue)
 - NTE30143 (White)
 - NTE30144 (Pink)
 - NTE30145 (UV/Purple)

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Power Dissipation, P_D	80mW
Peak Forward Current (1/10th Duty Cycle, 0.1ms Pulse Width), I_{FM}	100mA
Continuous Forward Current, I_F	25mA
Derating Linear from $+30^\circ\text{C}$	0.8mA/ $^\circ\text{C}$
Reverse Voltage, V_R	5V
Operating Temperature Range, T_{opr}	-20° to $+80^\circ\text{C}$
Storage Temperature Range, T_{stg}	-30° to $+100^\circ\text{C}$
Lead Temperature (During Soldering, 1.6mm from Body, 5sec Max), T_L	$+260^\circ\text{C}$

Electrical Optical Characteristics: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Forward Voltage NTE30140	V_F	$I_F = 20\text{mA}$	2.0	–	2.2	V
All Others			3.0	–	3.2	V
Luminous Intensity NTE30140	I_V	$I_F = 20\text{mA}$	500	–	800	mcd
NTE30141			5000	–	7000	mcd
NTE30142			1000	–	1500	mcd
NTE30143			4000	–	6000	mcd
NTE30144			300	–	400	mcd
NTE30145			100	–	150	mcd
Peak Emission Wavelength NTE30140	λ_P		620	–	630	nm
NTE30141			515	–	525	nm
NTE30142			460	–	470	nm
NTE30143			8000	–	12000	K
NTE30145			390	–	410	nm
Half Intensity Angle	$2 \theta_{1/2}$		–	30	–	deg

Rev. 9-17



