

222AT6

M

DRAWING NUMBER

3

ISSUE

REVISIONS

A PR-10832

J A P

31 DEC 81

B C082984

DLT

23 MAY 96

FO-3285 1-B

DRAWN

J A P

31 DEC 81

CHECK

4 JAN 82

CHECK



REPLACES

RELEASE NO. PR-10832



MICRO SWITCH
 FREEPORT ILLINOIS, U S A
 A DIVISION OF HONEYWELL
 FED. MFG. CODE 91929

ASSEMBLY - TOGGLE SWITCH

CATALOG LISTING
222AT6



N.O. TO C. CIRCUITS MADE, (SW. NO. 4, 5 & 6)
 N.C. TO C. CIRCUITS MADE, (SW. NO. 1, 2 & 3)
 (MAINTAINED POSITION)



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH

CHARACTERISTICS		ELECTRICAL DATA			
		CONTACT ARRANGEMENT (6) SPDT			
LOAD	SEA LEVEL		70,000 ft.		
	28 VDC	115 VAC, 400 CPS	28 VDC		
RES.	4 AMP	2 AMP	4 AMP		
IND.	2 AMP	2 AMP	2 AMP		
LAMP	1 AMP	.5 AMP	1 AMP		

SCALE FULL			
DO NOT SCALE PRINT			
TOLERANCES			
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE UNLESS NOTED. TOLERANCES ARE 2			
DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/64	X
ONE PLACE	X,X	0.001	X,X
TWO PLACES	X,XX	0.0005	X,XX
THREE PLACES	X,XXX	0.0001	X,XXX
ANGLES			
SI METRIC		US CUSTOMARY	
DESIGN UNITS		THIRD ANGLE PROJECTION	
			
WEIGHT			

- NOTES**
- 1 - UNIT INCLUDES (6) CAT. LIST. 1HM19 BASIC SWITCHES
 - 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
 - 3 - TERMINALS ARE PLATED FOR SOLDERING