


Small Signal Zener Diodes



MARKING (example only)



23210 Cathode mark

X.Y = type code
Y4 = date code

LINKS TO ADDITIONAL RESOURCES



3D Models



Models

FEATURES

- Silicon planar Zener diodes
- Standard Zener voltage tolerance is $\pm 5\%$
- AEC-Q101 qualified available (part number on request)
- ESD capability according to AEC-Q101:
Human body model $> 8\text{ kV}$
Machine model $> 800\text{ V}$
- Base P/N-G3 - green, commercial grade
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

PRIMARY CHARACTERISTICS

PARAMETER	VALUE	UNIT
V_Z range nom.	2.4 to 43	V
Test current I_{ZT}	0.05	mA
V_Z specification	Thermal equilibrium	
Circuit configuration	Single	

ORDERING INFORMATION

DEVICE NAME	ORDERING CODE	TAPED UNITS PER REEL	MINIMUM ORDER QUANTITY
MMSZ4681 to MMSZ4717	MMSZ4681-G3-08 to MMSZ4717-G3-08	3000 (8 mm tape on 7" reel)	15 000/box
	MMSZ4681-G3-18 to MMSZ4717-G3-18	10 000 (8 mm tape on 13" reel)	10 000/box

PACKAGE

PACKAGE NAME	WEIGHT	MOLDING COMPOUND FLAMMABILITY RATING	MOISTURE SENSITIVITY LEVEL	SOLDERING CONDITIONS
SOD-123	10.6 mg	UL 94 V-0	MSL level 1 (according J-STD-020)	Peak temperature max. 260 °C

ABSOLUTE MAXIMUM RATINGS ($T_{amb} = 25\text{ °C}$, unless otherwise specified)

PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT
Power dissipation	$R_{thJA} = 250\text{ K/W}$	P_{tot}	500	mW
	On FR-4 board with recommended soldering footprint	P_{tot}	300	mW
Thermal resistance junction to lead		R_{thJL}	250	K/W
Thermal resistance junction to ambient	According to JEDEC® 51-3 on FR-4 board with recommended soldering footprint	R_{thJA}	420	K/W
Junction temperature		T_j	150	°C
Storage temperature range		T_{stg}	-65 to +150	
Operating temperature range		T_{op}	-55 to +150	

**ELECTRICAL CHARACTERISTICS** ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)

PART NUMBER	MARKING CODE	ZENER VOLTAGE RANGE ⁽¹⁾			TEST CURRENT	REVERSE CURRENT	
		V_Z at I_{ZT1}			I_{ZT1}	I_R at V_R	
		V			mA	μA	V
		MIN.	NOM.	max.		MAX.	
MMSZ4681-G	TF	2.28	2.4	2.52	0.05	2	1
MMSZ4682-G	TH	2.57	2.7	2.84	0.05	1	1
MMSZ4683-G	TJ	2.85	3	3.15	0.05	0.8	1
MMSZ4684-G	TK	3.14	3.3	3.47	0.05	7.5	1.5
MMSZ4685-G	TM	3.42	3.6	3.78	0.05	7.5	2
MMSZ4686-G	TN	3.71	3.9	4.1	0.05	5	2
MMSZ4687-G	TP	4.09	4.3	4.52	0.05	4	2
MMSZ4688-G	TT	4.47	4.7	4.94	0.05	10	3
MMSZ4689-G	TU	4.85	5.1	5.36	0.05	10	3
MMSZ4690-G	TV	5.32	5.6	5.88	0.05	10	4
MMSZ4691-G	TA	5.89	6.2	6.51	0.05	10	5
MMSZ4692-G	TX	6.46	6.8	7.14	0.05	10	5.1
MMSZ4693-G	TY	7.13	7.5	7.88	0.05	10	5.7
MMSZ4694-G	TZ	7.79	8.2	8.61	0.05	1	6.2
MMSZ4695-G	UC	8.27	8.7	9.14	0.05	1	6.6
MMSZ4696-G	UD	8.65	9.1	9.56	0.05	1	6.9
MMSZ4697-G	UE	9.5	10	10.5	0.05	1	7.6
MMSZ4698-G	UF	10.5	11	11.6	0.05	0.05	8.4
MMSZ4699-G	UH	11.4	12	12.6	0.05	0.05	9.1
MMSZ4700-G	UJ	12.4	13	13.7	0.05	0.05	9.8
MMSZ4701-G	UK	13.3	14	14.7	0.05	0.05	10.6
MMSZ4702-G	UM	14.3	15	15.8	0.05	0.05	11.4
MMSZ4703-G	UN	15.2	16	16.8	0.05	0.05	12.1
MMSZ4704-G	UP	16.2	17	17.9	0.05	0.05	12.9
MMSZ4705-G	UT	17.1	18	18.9	0.05	0.05	13.6
MMSZ4706-G	UU	18.1	19	20	0.05	0.05	14.4
MMSZ4707-G	UV	19	20	21	0.05	0.01	15.2
MMSZ4708-G	UA	20.9	22	23.1	0.05	0.01	16.7
MMSZ4709-G	UZ	22.8	24	25.2	0.05	0.01	18.2
MMSZ4710-G	UY	23.8	25	26.3	0.05	0.01	19
MMSZ4711-G	ZA	25.7	27	28.4	0.05	0.01	20.4
MMSZ4712-G	ZC	26.6	28	29.4	0.05	0.01	21.2
MMSZ4713-G	ZD	28.5	30	31.5	0.05	0.01	22.8
MMSZ4714-G	ZE	31.4	33	34.7	0.05	0.01	25
MMSZ4715-G	ZF	34.2	36	37.8	0.05	0.01	27.3
MMSZ4716-G	ZH	37.1	39	41	0.05	0.01	29.6
MMSZ4717-G	ZJ	40.9	43	45.2	0.05	0.01	32.6

Notes

- Maximum $V_F = 0.9\text{ V}$ at $I_F = 10\text{ mA}$
- (1) Measured with device junction in thermal equilibrium typ. R_{thJA} of 370 K/W


TYPICAL CHARACTERISTICS ($T_{amb} = 25\text{ }^{\circ}\text{C}$, unless otherwise specified)


Fig. 1 - Admissible Power Dissipation vs. Ambient Temperature






Fig. 2 - Thermal Impedance vs. Time

PACKAGE DIMENSIONS in millimeters (inches): **SOD-123**


Created - Date: 18.Oct.2021
Rev. 01 - Date: 18.Jan.2022
Document no.: S8-V-3910.01-003 (4)




ORIENTATION IN CARRIER TAPE




Created - Date: 09. Feb. 2016
Rev. 01 - Date: 07. Nov. 2022
Document no.: S8-V-3717.10-003 (4)


CARRIER TAPE



A-A Section



B-B Section



Created - Date: 07. Feb. 2013
Rev. 01 - Date: 01. Mar. 2014
Document no.: S8-V-3717.10-003 (4)



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.