molex



Part Number : 936014363
Product Description : Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 32B «77x62», M40x2 Thread, Grey
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7832.6385.0

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, with Gasket, Size 32B «77x62», M40x2 Thread, Grey
Component Type	Double Lever SMT Housing
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191894591

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V

Physical

Component Size	32B «77X62»
Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Gasket	NBR

Downloaded from Arrow.com.

Material - Housing	Die-cast Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Net Weight	686.000/g
Number of Levers	2
Packaging Type	Bag
Thread Size	M40x2
Thread Type	(M) Metric

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 32B «77x62» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K, S-M, and S-EHV Inserts

Downloaded from Arrow.com.