



REVISIONS			
REV	DESCRIPTION	DATE	CHANGED BY
H	ECN 4491: CN RELEASE	1/12/10	D. CASTRO
H	ECN99999: ADDED RoHS COMPLIANT STAMP	03/18/10	DFP
J	ECN5431: .660 WAS .618	04/08/11	DFP





MATERIAL:
HOUSING, LOAD BAR: POLYCARBONATE, CLEAR, UL94V-0
CONTACTS: PHOSPHOR BRONZE
SHIELD/STRAIN RELIEF: BRASS

CONTACTS: 50 MICROINCHES [1.27 MICRON] MIN. GOLD IN CONTACT AREA
OVER 100 MICROINCHES [2.54 MICRON] MIN. NICKEL PLATE OVERALL.
SHIELD/STRAIN RELIEF: 100 MICROINCHES [2.54 MICRON] NICKEL

VOLTAGE: 125 VAC. MAX.
CURRENT: 1.5 AMPS MAX.

CONTACT STYLE: 2 PRONG
COMPATIBLE WITH STRANDED AND SOLID CONDUCTORS
CONDUCTOR RANGE: 24 - 26 AWG
MAX. CONDUCTOR INSULATION DIAMETER: .042 [1.07]
PARTS SHALL CONFORM TO TIA-1096

OPERATING TEMPERATURE RANGE: -40°C TO +125°C
TERMINATED CONTACT HEIGHT: .237±.005 [6.02±.13]
FOR TERMINATION OR TOOLING INFORMATION PLEASE VISIT
THE APPROPRIATE PRODUCT PAGE AT WWW.L-COM.COM
PACKAGE PER SPEC. PS-0032



RoHS Compliant ✓

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]		APPROVALS DRAWN BY D. PARHAM 2/3/2004 CHECKED BY T. CLARK 2/3/2004 APPROVED BY C. MCCORMICK 2/3/2004		DATE 2/3/2004 2/3/2004 2/3/2004		GLOBAL Connectivity NORTH ANDOVER, MA 01845	
OVERALL CABLE LENGTH TOLERANCE: ≤ 12 [305] = +1 [25] / -0 > 12 [305] ≤ 40 [1524] = +2 [51] / -0 > 40 [1524] ≤ 120 [3048] = +4 [102] / -0 > 120 [3048] ≤ 300 [7620] = +6 [152] / -0 > 300 [7620] = +5% / -0%		ALL OTHER DIMENSIONAL TOLERANCES: $.X = \pm .2$ $.XX = \pm .02$ $.XXX = \pm .005$		CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		CATEGORY MODULAR	
PROJECTION 		COLOR VARIATIONS MAY OCCUR 1AD03-013		PRODUCT DESCRIPTION PLUG,RJ45 8X8 SHLD W/SR		SIZE B 43321	
				DWG. NO. TDS8PC5		REV. J	
				SCALE: 4:1 CAD FILE: TDS8PC5.SLDDRW		SHEET 1 OF 1	