

Waterproof Rocker Switches

Miniature Illuminated



Features


- **Waterproof:** IP65
- **Single Pole**
- **.187" Quick Connect Terminals**




NTE Type No.	Circuitry	Action			Material	Actuator Color		Vltg	Diag No.
						Neon	LED		
54-200W	SPST	ON	NONE	OFF	PC	Red	-	AC	S110
54-201W	SPST	ON	NONE	OFF	PC	-	Red	DC	S110
54-202W*	SPDT	ON	NONE	ON	PC	Black		N/A	S110
54-203W	SPST	ON	NONE	OFF	PC	Green	-	AC	S110
54-204W	SPST	ON	NONE	OFF	PC	-	Green	DC	S110

* Designates Non-Illuminated Type

S110



Wiring Diagram



Mounting Hole

Panel Thickness		X
.030 (.750) - .059 (1.50)		.764 (19.40)
.059 (1.50) - .098 (2.50)		.780 (19.80)

↓

.512
(13.0)

↑

←

X

→

Specifications

Current Rating: 16A 125VAC 1/3 HP, 10A 250VAC 1/2 HP

Lamp Voltage: 110V Neon (AC) & 12V LED (DC)

Insulation Resistance: 100 Megohms (min.) at 500VDC

Dielectric Strength: 1000V RMS (min.)

Temperature Rating: +32° to +185°F (0° to +85°C)

Electrical Life: 10,000 cycles

Mechanical Life: 50,000 cycles at full load

Terminal Type: .187" Tab Q.C.

Mounting Hole: See Table 1

Miniature Illuminated



Features


- **Waterproof:** IP66
- **Single Pole**
- **.250" Quick Connect Terminals**




NTE Type No.	Circuitry	Action			Material	Actuator Color		Vltg	Diag No.
						Neon	LED		
54-215W	SPST	ON	NONE	OFF	PC	Red	-	AC	S112
54-216W	SPST	ON	NONE	OFF	PC	-	Red	DC	S112
54-219W	SPST	ON	NONE	OFF	PC	Green	-	AC	S112
54-220W	SPST	ON	NONE	OFF	PC	-	Green	DC	S112
54-221W*	SPST	ON	NONE	OFF	PC	Black		N/A	S112

* Designates Non-Illuminated Type

S112



Wiring Diagram



Specifications

Current Rating: 20A 125VAC 1/3 HP, 10A 250VAC 3/4 HP,

20A 14VAC, 10A 24VAC

Lamp Voltage: 110V Neon (AC) & 12V LED (DC)

Insulation Resistance: 100 Megohms (min.) at 500VDC

Dielectric Strength: 1500V RMS (min.)

Temperature Rating: +32° to +185°F (0° to +85°C)

Electrical Life: 10,000 cycles

Mechanical Life: 50,000 cycles at full load

Terminal Type: .250" Tab Q.C.

Mounting Hole: 1.450 (36.8) x .600 (15.2)

Waterproof Rocker Switches

Round Illuminated



Features


- **Waterproof:** IP65
- **Single Pole**
- **.187" Quick Connect Terminals**



NTE Type No.	Circuitry	Action			Actuator			Diag No.
					Material	Color	Vltg	
54-503W*	SPST	ON	NONE	OFF	Nylon	Black	N/A	S117
54-526W	SPST	ON	NONE	OFF	Nylon	Green	- AC	S117
54-527W	SPST	ON	NONE	OFF	Nylon	- Red	DC	S117
54-529W	SPST	ON	NONE	OFF	Nylon	- Green	DC	S117
54-531W	SPST	ON	NONE	OFF	Nylon	Red	- AC	S117

* Designates Non-Illuminated Type

S117



Specifications

Current Rating: 16A 125VAC, 10A 250VAC
Lamp Voltage: 110V Neon (AC) & 12V LED (DC)
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: +32° to +185°F (0° to +85°C)
Electrical Life: 10,000 cycles
Mechanical Life: 50,000 cycles at full load
Terminal Type: .187" Tab Q.C.
Mounting Hole: .795 (20.2)

Round Illuminated



Features


- **Waterproof:** IP65
- **Double Pole**
- **.187" Quick Connect Terminals**



NTE Type No.	Circuitry	Action			Actuator			Diag No.
					Material	Color	Vltg	
54-205W	DPST	ON	NONE	OFF	PC	Red	- AC	S111
54-206W	DPST	ON	NONE	OFF	PC	- Red	DC	S111
54-209W	DPST	ON	NONE	OFF	PC	Green	- AC	S111
54-210W	DPST	ON	NONE	OFF	PC	- Green	DC	S111
54-211W*	DPST	ON	NONE	OFF	PC	Black	N/A	S111

* Designates Non-Illuminated Type

S111



Specifications

Current Rating: 16A 125VAC, 10A 250VAC
Lamp Voltage: 110V Neon (AC) & 12V LED (DC)
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: +32° to +185°F (0° to +85°C)
Electrical Life: 10,000 cycles
Mechanical Life: 50,000 cycles at full load
Terminal Type: .187" Tab Q.C.
Mounting Hole: .795 (20.2)

Waterproof Rocker Switches

Round Illuminated




Features

- Waterproof: IP65
- .250" Quick Connect Terminals



NTE Type No.	Circuitry	Action	Actuator			Diag No.
			Material	Color	Vltg	
54-739W	SPST	ON NONE OFF	PC	Neon - LED Red	AC	S146



Specifications

Current Rating: 16A 125VAC
Lamp Voltage: 110V
Insulation Resistance: 100 Megohms (min.) at 500VDC
Dielectric Strength: 1500V RMS (min.)
Temperature Rating: -13° to +185°F (-25° to +85°C)
Electrical Life: 6,000 cycles
Mechanical Life: 10,000 cycles
Terminal Type: .250" Tab Q.C.
Mounting Hole: .945 (24.0)

Dual Color Illuminated




Features

- IP67 Certified
- Single and Double Pole
- Dual Color Types
- .250" Quick Connect Terminals



NTE Type No.	Circuitry	Action	Actuator			Diag No.
			Material	Color	Vltg	
54-150	SPST	ON NONE OFF	Nylon	- Amber/Green	DC	S116
54-151	SPST	(ON) NONE OFF	Nylon	- Amber/Green	DC	S116
54-153	SPDT	ON OFF ON	Nylon	- Amber/Green	DC	S116
54-154	SPDT	ON OFF (ON)	Nylon	- Amber/Green	DC	S116
54-157	DPDT	ON NONE ON	Nylon	- Amber/Green	DC	S116
54-158	DPDT	(ON) OFF (ON)	Nylon	- Amber/Green	DC	S116

SPECIAL NOTE: () = Momentary Function



Specifications

Current Rating: 20A 12VDC,
Lamp Voltage: 12V LED (DC)
Insulation Resistance: 50 Megohms
Dielectric Strength:
Between Pole to Pole: 1250 VRMS
Between Live Parts & Accessible Surfaces: 3750 VRMS
Temperature Rating: -40° to +185°F (-40° to +85°C)
Electrical Life: 100,000 cycles maintained
50,000 cycles momentary at rated voltage & current
Mechanical Life: 250,000 cycles min.
Terminal Type: .250" Tab Q.C.
Mounting Hole: 1.734 (44.04) x .867 (22.02)

Waterproof Rocker Switches

Illuminated & Non-Illuminated



Features


- **Waterproof:** IP66 (Note 1)
- **Single and Double Pole**
- **Available in Single and Dual Color Types**
- **.250" Quick Connect Terminals**



NTE Type No.	Circuitry	Action			Actuator			Diag No.
					Material	Color	Vltg	
						Neon	LED	
54-225W*	SPST	ON	NONE	OFF	PC	Black		N/A S113
54-226W*	DPDT	ON	NONE	ON	PC	Black		S113
54-227W*	SPDT	ON	NONE	ON	PC	Black		S113
54-228W#	SPDT	ON	OFF	ON	PC	Black		S113
54-229W*	DPDT	ON	OFF	ON	PC	Black		S113
54-230W	SPST	ON	NONE	OFF	PC	Red		AC S113
54-231W	SPST	ON	NONE	OFF	PC		Red	DC S113
54-232W	SPST	ON	NONE	OFF	PC	Green		AC S113
54-233W	SPST	ON	NONE	OFF	PC		Green	DC S113
54-234W	SPST	ON	NONE	OFF	PC	Blue		AC S113
54-235W	SPST	ON	NONE	OFF	PC		Blue	DC S113
54-238W#	SPDT	ON	NONE	ON	PC	Rd/Gn		AC S113
54-239W	SPDT	ON	NONE	ON	PC		Rd/Gn	DC S113
54-240W	SPDT	ON	OFF	ON	PC	Rd/Gn		AC S113
54-241W	SPDT	ON	OFF	ON	PC		Rd/Gn	DC S113
54-246W	SPDT	ON	NONE	ON	PC	Rd/Rd		AC S113
54-247W	SPDT	ON	NONE	ON	PC		Rd/Rd	DC S113
54-248W	SPDT	ON	OFF	ON	PC	Rd/Rd		AC S113
54-249W	SPDT	ON	OFF	ON	PC		Rd/Rd	DC S113
54-250W*	DPDT	(ON)	OFF	(ON)	PV	Black		N/A S113

* Designates Non-Illuminated Type
SPECIAL NOTE: () = Momentary Function
Note 1: 54-228W & 54-241W are IP56


S113





Mounting Hole

Table 1.

Panel Thickness	Y
.030 (.750) - .049 (1.25)	1.441 (36.6)
.049 (1.25) - .079 (2.00)	1.449 (36.8)
.079 (2.00) - .118 (3.00)	1.457 (37.0)



Wiring Diagram



Specifications

Current Rating: 21A 14VDC

20A, 125VAC (54-228W & 54-238W Only)

Lamp Voltage: 110V Neon (AC) & 12V LED (DC)

Insulation Resistance: 100 Megohms (min.) at 500VDC

Dielectric Strength: 1500V RMS (min.)

Temperature Rating: +32° to +149°F (0° to +65°C)
+68° to +185°F (+20° to +85°C) (54-228W Only)

Electrical Life: 10,000 cycles

Mechanical Life: 50,000 cycles at full load

Terminal Type: .250" Tab Q.C.

Mounting Hole: See Table 1