Part Number : 1200060560
Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Pigtail, 0.34mm² Black PVC Cable, 2.0m (6.56') Length
Series Number : 120006
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 804006E03M020



Documents and Resources

Drawings

1200060560_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120006
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, A-Coded, Male (Straight) to Pigtail, 0.34mm^2 Black PVC Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	883906067984

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.40mm (.213")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail

Downloaded from Arrow.com.

Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	102.100/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-30° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	22

Downloaded from Arrow.com.