

Wire & Cable > Hook Up Wire > SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire



Cable Type: **MIL-DTL-22759**

Operating Voltage: **600 V**

Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**

Conductor Material: **Nickel-Coated Copper**

Wire Size: **20 AWG**

[All SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire \(235\)](#)

Features

Product Type Features

Cable Style	Primary
-------------	---------

Configuration Features

Number of Strands	19
-------------------	----

Number of Conductors	1
----------------------	---

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
----------------------------------	--

Conductor Material	Nickel-Coated Copper
--------------------	----------------------

Wire Color (Base)	White
-------------------	-------

Dimensions

	.009 in
Strand Size	32 AWG
Outside Cable Diameter	1.47 mm [.058 in]
Conductor Diameter Range	1.01 mm [.04 in]

Wire Size	20 AWG
-----------	--------

Usage Conditions

Cable Type	MIL-DTL-22759
Operating Temperature Range	-65 – 200 °C [-85 – 392 °F]

Other

Product Source	US
----------------	----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # A36675-000
D-200-83

Customers Also Bought



TE Part #916219-000
D-621-0453



TE Part #CAT-AS22759-34
SAE AS22759: 34/35/41/42/43 - Dual-Wall, Normal Weight Wire



TE Part #ABC06O-20P-4048
IN-LINE PLUG



TE Part #1616081-1
A1077B (FAA/PMA)=RELAY



TE Part #1616109-4
A700AQ4=RELAY



TE Part #CTJ420E044-513
ELEC MODULE



TE Part #C04237-000
D-500-0465-1-613-240-TCS2692



TE Part #669835-000
2524A0424-9XCS2471



TE Part #ES4050402BGM
ES4050402BGM=RELAY

Documents

Product Drawings

22759/41-20-9

English

Datasheets & Catalog Pages

Raychem Wire and Cable Quick Reference Guide

English