



**Part Number :** [1451300703](#)

**Product Description :** Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Single Row, Matte Tin (Sn) Plating, 300.00mm Length, 7 Circuits, Black

**Series Number :** 145130

**Status :** Active

**Product Category :** Power and Signal Cable Assemblies

---

## Documents and Resources

### Drawings

[1451300703 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

### [Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Power and Signal Cable Assemblies
Series	145130
Description	Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Single Row, Matte Tin (Sn) Plating, 300.00mm Length, 7 Circuits, Black
Application	Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Fit-to-Nano-Fit
Product Name	Nano-Fit
Type	Discrete Wire Assembly
UPC	191130118991

### Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	250V AC (RMS)

### Physical

Cable Length	300.00mm
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Black

Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	High Conductivity Copper
Material - Plating Mating	Matte Tin
Material - Plating Termination	Matte Tin
Material - Resin	Nylon
Net Weight	18.221/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1061
Wire Size (AWG)	20

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 7 Circuits, with Kinked Pins, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray	<u>1053091107</u>
Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Single Row, 7 Circuits, with Solder Clips, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray	<u>1053111107</u>
Nano-Fit Right-Angle Header, Through Hole, 2.50mm Pitch, Single Row, 7 Circuits, Tin (Sn) Plating, Black, Glow-Wire Capable, Tray	<u>1053131107</u>
Nano-Fit Vertical Header, Surface	<u>1054311107</u>

Mount, 2.50mm Pitch, Single Row, 7 Circuits, 0.76µm Tin (Sn) Plating, with Pick-and-Place Tape, Black, Glow-Wire Capable	
Nano-Fit Right-Angle Header, Surface Mount, 2.50mm Pitch, Single Row, 7 Circuits, 0.76µm Tin (Sn) Plating, Black, Glow-Wire Capable	<u>1054301107</u>
Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Single Row, 7 Circuits, Black, Glow-Wire Capable	<u>2002771107</u>
Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Single Row, 7 Circuits, Black, Panel Mount, Glow-Wire Capable	<u>2002771207</u>

---

This document was generated on May 20, 2026