




Part Number : [5047542520](#)

Product Description : Easy-On Back Flip FPC Connector, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 25 Circuits

Series Number : 504754

Status : Active

Product Category : FFC / FPC Connectors



Documents and Resources

Drawings

[5047542520 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[5047542520.dxf](#)

Specifications

[AS-504754-002-001.pdf](#)

[5047549200-200.pdf](#)

[PS-504754-002-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	FFC / FPC Connectors
Series	LA75
Description	Easy-On Back Flip FPC Connector, 0.30mm Pitch, LA75 Series, Right-Angle, Surface Mount, Dual Contact Style, 0.75mm Height, 25 Circuits
Product Name	Easy-On
UPC	889056511476

Electrical

Current - Maximum per Contact	0.3A
Voltage - Maximum	50V

Physical

Actuator Type	Back Flip
Circuits (Loaded)	25
Color - Resin	Black
Contact Position	Dual

Durability (mating cycles max)	10
Mated Height	0.75mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	31.603/mg
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	No
Pitch - Mating Interface	0.30mm
Pitch - Termination Interface	0.30mm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire/Cable Type	FPC only

This document was generated on May 16, 2026