

# Cleaning Brushes



## Description

MG Chemicals brushes enhance the delivery of chemical cleaners and remove loose debris that cleaners alone cannot. The bristles come in stainless steel, brass, horse, or hog hair. The brush handles come in a selection of wood, stainless steel, cad plated steel, or tin. Depending on the application, the brushes offer abrasive, non-abrasive, or anti-static properties.




## Features & Benefits

- Durable
- Secured bristles eliminate bristle loss and contamination
- Robust handles
- Anti-static—Cat No. 852, 855, 856, 857, and 859

## Bristle Materials

Stainless Steel	Highly abrasive bristles that are resistant to heat, rust, and corrosion
Brass	Abrasive and flexible bristles that are good for soft metal surfaces
Hog Hair	Fairly stiff hair, non-abrasive bristles with excellent durability, and water resistance. Heat tolerant to 188 °C.
Horse Hair	Durable, soft to slightly stiff bristles that can be used for scratch-free dry brushing and polishing. It is not resistant to acids or alkalis. Heat tolerant to 188 °C.




## Available Packaging

	Part #	Trim	Row	Brush Face (L x W)	Handle (L x W)	Handle Material	Quantity
<b>Stainless Steel Cleaning Brush</b> 	850	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	5
<b>Brass Cleaning Brush</b> 	851	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	5
<b>Hog Hair Cleaning Brush</b> 	852	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	5

# Cleaning Brushes



## Available Packaging

	Part #	Trim	Row	Brush Face (L x W)	Handle (L x W)	Handle Material	Quantity
<b>Horse Hair Cleaning Brush</b>							
	855-5	3/4"	—	1/2" (W)	5 1/4" x 3/8"	Tin	5
	855-144	3/4"	—	1/2" (W)	5 1/4" x 3/8"	Tin	144
<b>Double Horse Hair Cleaning Brush</b>							
	856	1/4"	—	1/2" (W)	4 1/2"	Stainless steel	5
<b>Chisel Hog Hair Cleaning Brush</b>							
	857	1/2"	2 x 6	7/8" x 3/8"	4 15/16" x 1 1/16"	Plywood	5
<b>Horse Hair Cleaning Brush</b>							
	859	7/16"	3 x 7	1 3/8" x 1/4"	7 3/4" x 7/16"	Plywood	5

**Disclaimer:** This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

**MG Chemicals** 1210 Corporate Drive Burlington, Ontario, Canada L7L 5R6 ISO 9001:2015 Quality Management System SAI Global File: 004008  
 support@mgchemicals.com **North America** +(1) 800-340-0772 **International** +(1) 905-331-1396 **Europe** +44 1663 362888 20 October 2025 / Ver. 2.1