










PRODUCT NUMBER SEE SHEET 2




spec ref *				dr <a href="#">Vicki Liu</a>		2015/12/27		projection				size A3		scale 3:2			
tolerance std				eng <a href="#">Vicki Liu</a>		2016/01/29						ecn no -					
ASME Y14.5				chr <a href="#">Fancy Zhang</a>		2016/01/29											
				appr <a href="#">Pei-Ming Zheng</a>		2016/01/29											
TOLERANCES UNLESS OTHERWISE SPECIFIED				product family				PwrBlade+				rel level <b>Released</b>					
surface 		linear		0.X		±0.5				title IHP + 16S + IHP PMT		dwg no 10106125-2004001		rev <b>A</b>			
		0.XX		±0.25													
		0.XXX		±0.10													
ASME Y14.5		angular		0°		±2°		www.fci.com		cat. no.		Product - Customer Drw				sheet 1 of 3	



Copyright FCI.

CODE	DESCRIPTION
FA	FMLB SIGNAL CONTACT, ROW A (3.05)
FB	FMLB SIGNAL CONTACT, ROW B (3.05)
FC	FMLB SIGNAL CONTACT, ROW C (3.05)
FD	FMLB SIGNAL CONTACT, ROW D (3.05)
HE	STD HIGH POWER CONTACT (3.05)
SA	STD SIGNAL CONTACT, ROW A (3.05)



dr	Vicking Liu	2015/12/27	projection	MM	size	A3	scale	3:2
eng	Vicking Liu	2016/01/29			ecn no	-		
chr	Fancy Zhang	2016/01/29			rel level	Released		
appr	Pei-Ming Zheng	2016/01/29	product family	PwrBlade+				
www.fci.com	cat. no.	IHP + 16S + IHP PMT			dwg no	10106125-2004001	rev	A
Product - Customer Drw			sheet 2 of 3					

A

B

C

D

A


B

C

D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.  
THE MARK CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:  
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.  
-SIGNAL CONTACT - COPPER ALLOY.  
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION: 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS ARE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ±0.025MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn  
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ±0.07MM HOLE.
- 8) PRODUCT SPECIFICATION: GS-12-658.  
APPLICATION SPECIFICATION: GS-20-141.  
PRODUCT PACKAGED IN TRAYS: GS-14-1502.



dr	Vicking Liu	2015/12/27	<div>projection</div> <div></div>	<div>MM</div> <div></div>	size	A3	scale	3:2		
eng	Vicking Liu	2016/01/29			ecn no	-				
chr	Fancy Zhang	2016/01/29								
appr	Pei-Ming Zheng	2016/01/29	product family	PwrBlade+	rel level	Released				
<div>www.fci.com</div>			<div>FCi</div>			<div>title</div> <div>IHP + 16S + IHP PMT</div> <div>RA PF HEADER</div>			<div>dwg no</div> <div>10106125-2004001</div>	<div>rev</div> <div>A</div>
<div>cat. no.</div>			<div>Product - Customer Drw</div>			<div>sheet 3 of 3</div>				