



+ CONNECTORS

HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)
CT RELAY HDR ASSY 15P BLUE

AMP CT | AMP CT

3-292254-5
TE Internal Number: 3-292254-5

EU RoHS Compliant
EU ELV Compliant

Connector System Wire-to-Board, Wire-to-Panel, Wire-to-Wire

Number of Positions 15

Centerline (Pitch) (mm) 2

Number of Rows 1

Contact Mating Area Plating Material Tin

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

PANEL MOUNT TYPE RELAY POST HEADER ASS'Y (AMP CT CONNECTOR 2mm PITCH)

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

TIF

Japanese

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

PDF

Japanese

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board, Wire-to-Panel, Wire-to-Wire

Header Type Feed Through, Shrouded

Sealable No

Product Type Connector

Connector Type Header

Shape Rectangular

Connector Style Plug

Wire/Cable Type Discrete Wire

Configuration Features

Number of Positions 15

Number of Rows 1

Backwall/Post Interruptions Without

Electrical Characteristics

Operating Voltage (VAC) 125

Operating Voltage (VDC) 125

Contact Features

Contact Shape Round
Contact Mating Area Plating Material Tin
Contact Mating Area Plating Thickness 1 µm [39.37 µin]
Contact Current Rating (Max) (A) 4
Contact Base Material Brass
Contact Termination Area Plating Material Tin
Contact Transmits (Typical) Signal (Data)
Contact Design Round Post
Tail Plating Material Tin
Contact Type Pin

Mechanical Attachment

Panel Mount Retention With
Mating Retention Without
Connector Mounting Type Panel
Mating Alignment With
Mating Retention Type Locking Latch
Mating Alignment Type Polarization
Contact Retention Without

Housing Features

Centerline (Pitch) (mm) 2
Housing Material Nylon 66
Housing Color Blue

Dimensions

Height 12 mm [.472 in]
Width 6 mm [.236 in]
Length 33.78 mm [1.329 in]
Wire/Cable Size (AWG) 30 – 22
Mating Post Length 4.5 mm [.177 in]

Usage Conditions

Operating Temperature Range -40 – 105 °C [-40 – 105 °F]

Operation/Application

Pick and Place Cover Internal
For Use With MT Connector

Industry Standards

Agency/Standard UL 94V-0, UL
CSA File Number LR 7189
UL Flammability Rating UL 94V-0
Agency/Standard Number CSA, UL
UL File Number E28476

Packaging Features

Packaging Reel Diameter 300
Packaging Method Bag/Box
Packaging Quantity 300



Statement of Compliance

Statement of Compliance

PDF