



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Interface Seal**
Operating Temperature Range: **-30 – 140 °C [-22 – 284 °F]**
Primary Product Color: **Blue**
Primary Product Material: **Silicone Rubber**
Operating Temperature (Max): **140 °C [284 °F]**

Features

Product Type Features

Connector Seal & Plug Type	Interface Seal
----------------------------	----------------

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Blue
Primary Product Material	Silicone Rubber

Usage Conditions

Operating Temperature Range	-30 – 140 °C[-22 – 284 °F]
Operating Temperature (Max)	140 °C[284 °F]

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250)



Candidate List Declared Against: JUNE 2025 (250)
SVHC > Threshold:
Dodecamethylcyclhexasiloxane (D6) (.5% in M-45547-1)
Decamethylcyclopentasiloxane (D5) (.5% in M-45547-1)
Octamethylcyclotetrasiloxane (D4) (.5% in M-45547-1)

Article Safe Usage Statements:
Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2-2378159-3 Power Versa-Lock PLUG, 1X3 KEY B	 TE Part # 1-2336229-6 Power Versa-Lock PLUG, 2X3 KEY A	 TE Part # 1-2381315-3 Power Versa-Lock PLUG, 1X3 KEY A, GWT	 TE Part # 2-2378158-3 Power Versa-Lock CAP, 1X3 KEY B
 TE Part # 3-2378158-3 Power Versa-Lock CAP, 1X3 KEY C	 TE Part # 1-2378158-3 Power Versa-Lock CAP, 1X3 KEY A	 TE Part # 3-2336229-6 Power Versa-Lock PLUG, 2X3 KEY C	 TE Part # 2-2336229-6 Power Versa-Lock PLUG, 2X3 KEY B



TE Part # 1-2378159-3
Power Versa-Lock PLUG, 1X3 KEY A

TE Part # 3-2378159-3
Power Versa-Lock PLUG, 1X3 KEY C

Also in the Series

Power Versa-Lock 5.0

Connector Contacts(12)

Connector Hardware(5)

Connector Seals & Cavity Plugs(10)

Power Contacts(12)

Rectangular Connector Housings(77)

Rectangular Power Connectors(77)

Standard Rectangular Connectors(77)

Customers Also Bought

TE Part #816484-SF
RN102-0.3-02-12M

TE Part #42100-2
FF 250 REC 18-14AWG TPBR

TE Part #180907
FF 250 REC HSG 2P NYLON NAT

TE Part #350810-1
05P UMNL CAP HSG

TE Part #9-1879517-0
CRGH1206 1% 22R 0.5W

TE Part #2-2176348-5
CRGCQ 2010 10K 5%

TE Part #2176492-9
BMC 0402 120R 25% A Gen C

TE Part #2376595-2
250 FASTON PCB TAB TPBR



Documents

Product Drawings

Power Versa-Lock INTERFACE SEAL, 1X3

English

CAD Files

Customer View Model

ENG_CVM_CVM_2325347-3_A1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2325347-3_A1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2325347-3_A1.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

power-versa-lock-connectors-0421

English

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English