

Basic Switch Common Accessories

Separator (Sold Separately)

To ensure a secure insulation distance, or if there are other metal parts or copper wire installed too close to the Switch, use a separator purchased separately to keep the insulation distance.


■List of models

Appearance	Applicable Switches	Thickness (mm)	Model
 Separator	V D3V-01 VX D2RV D2VW	0.13	SEPARATOR FOR V T0.13
 Separator	SS SS-P D2S D2SW D2SW-P	0.13	SEPARATOR FOR SS T0.13


Note. The Separator is made of insulating cloth.

■Dimensions (Unit: mm)

SEPARATOR FOR V T0.13



SEPARATOR FOR SS T0.13



Note. The dimensions in the above outline drawings are reference values.

Downloaded from Arrow.com.


Basic Switch Common Accessories

Actuator (Sold Separately)

Actuators are supplementary components used when operating the Switch using cams or dogs or when transmitting mechanical movements that are not in alignment with the switch plunger.
The VAL models are suitable for cases where a Switch is operated by a rotary cam or sliding devices with relatively low operation frequency.
The VAM models are designed to operate in reverse movements and have high shock and vibration resistance. Since the Overtravel (OT) of these models is rather large, they can be used for automatic control or door switches of machining tools.

The VAV models can be used where a small Operating Force (OF) is required.

These Actuators do not include Switches.





Note. Switches with the mounting holes shown in the diagram can be used except for special models.

■Dimensions (Unit: mm) / Operating Characteristics

* Model numbers are for the Actuators only.
The value given for operating characteristics are reference values. For operating characteristics of models not listed above, consult your OMRON sales representative.

●Leaf Spring Model
VAL







Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	2.26 N {230 gf}
Releasing Force	RF	Min.	0.49 N {50 gf}
Overtravel	OT	Min.	0.8 mm
Movement Differential	MD	Max.	0.4 mm
Free Position	FP	Max.	17 mm
Operating Position	OP		14.9±0.5 mm

Note. Pin plunger (Designed for models of OF 1.96 N {200 gf} or greater).

●Simulated Leaf Spring
VAL12







Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	2.26 N {230 gf}
Releasing Force	RF	Min.	0.49 N {50 gf}
Overtravel	OT	Min.	0.8 mm
Movement Differential	MD	Max.	0.4 mm
Free Position	FP	Max.	22.9 mm
Operating Position	OP		20.5±0.8 mm

Note. Pin plunger (Designed for models of OF 1.96 N {200 gf} or greater).

●Roller Leaf Spring
VAL2
VAL02






Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	2.26 N {230 gf}
Releasing Force	RF	Min.	0.49 N {50 gf}
Overtravel	OT	Min.	0.8 mm
Movement Differential	MD	Max.	0.4 mm
Free Position	FP	Max.	22.6 mm
Operating Position	OP		20.5±0.5 mm

Note. Pin plunger (Designed for models of OF 1.96 N {200 gf} or greater).

Note1. Unless otherwise specified, a tolerance of ±0.4mm applies to all dimensions.
Note2. The operating characteristics are for operation in the A direction (⬇).

Downloaded from Arrow.com.


●Long Hinge Lever
VAV



Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	0.34 N {35 gf}
Releasing Force	RF	Min.	0.04 N {4 gf}
Pretravel	PT	Max.	7.6 mm
Overtravel	OT	Min.	3.6 mm
Movement Differential	MD	Max.	4.7 mm
Operating Position	OP		Approx. 10.6 mm

Note. Pin plunger designed for models of OF 0.98 N {100 gf} or greater.
Use in direction where the lever does not apply its own weight load to the plunger.


●Hinge Wire Lever
VAV-5



Operating characteristics			In the case of VX-5-1A2
Operating Force	OF	Max.	0.03 N {3 gf}
Pretravel	PT	Max.	16 mm
Overtravel	OT	Min.	2 mm
Movement Differential	MD	Max.	5 mm
Operating Position	OP		Approx. 16.7 mm

Note. This is designed for model of OF 0.25 N {25 gf}.
Use in direction where the lever does not apply its own weight load to the plunger.


●Hinge Roller Lever
VAV2



Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	0.74 N {75 gf}
Releasing Force	RF	Min.	0.09 N {9 gf}
Pretravel	PT	Max.	4.8 mm
Overtravel	OT	Min.	1.5 mm
Movement Differential	MD	Max.	1.2 mm
Operating Position	OP		18.6±1.6 mm

Note. Pin plunger designed for models of OF 0.98 N {100 gf} or greater.
Use in direction where the lever does not apply its own weight load to the plunger.


●Reverse Long Hinge Lever
VAM



Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	1.96 N {200 gf}
Releasing Force	RF	Min.	0.29 N {30 gf}
Overtravel	OT	Min.	7mm (reference value)
Movement Differential	MD	Max.	5mm
Free Position	FP	Max.	45 mm
Operating Position	OP		20±9 mm

Note. Not available for D2VW.

●Reverse Hinge Lever
VAM21



Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	3.53 N {360 gf}
Releasing Force	RF	Min.	0.69 N {70 gf}
Overtravel	OT	Min.	5 mm (reference value)
Movement Differential	MD	Max.	4 mm
Free Position	FP	Max.	30 mm
Operating Position	OP		20±4 mm


Note. Not available for D2VW.


Note1. Unless otherwise specified, a tolerance of ±0.4mm applies to all dimensions.
Note2. The operating characteristics are for operation in the A direction (⬇).

Downloaded from Arrow.com.

Basic Switch Common Accessories

●Reverse Hinge Modified Lever
VAM-1







Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	2.94 N {300 gf}
Releasing Force	RF	Min.	0.39 N {40 gf}
Overtravel	OT	Min.	5 mm (reference value)
Movement Differential	MD	Max.	6 mm
Free Position	FP	Max.	47 mm
Operating Position	OP		30±5 mm

Note. Not available for D2VW.

●Reverse Roller Modified Lever
VAM22







Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	3.53 N {360 gf}
Releasing Force	RF	Min.	0.69 N {70 gf}
Overtravel	OT	Min.	3 mm (reference value)
Movement Differential	MD	Max.	4 mm
Free Position	FP	Max.	38 mm
Operating Position	OP		31±3 mm

Note. Not available for D2VW.

●Reverse Long Hinge Roller Lever
VAM2





Operating characteristics			In the case of V-15-1A5
Operating Force	OF	Max.	2.45 N {250 gf}
Releasing Force	RF	Min.	0.39 N {40 gf}
Overtravel	OT	Min.	7 mm (reference value)
Movement Differential	MD	Max.	6 mm
Free Position	FP	Max.	48 mm
Operating Position	OP		31±6 mm

Note. Not available for D2VW.

Note1. Unless otherwise specified, a tolerance of ±0.4mm applies to all dimensions.
Note2. The operating characteristics are for operation in the A direction (⬇).

Please check each region's Terms & Conditions by region website.

OMRON Corporation
Device & Module Solutions Company

Regional Contact

Americas
https://components.omron.com/us
Asia-Pacific
https://components.omron.com/ap
Korea
https://components.omron.com/kr
Europe
https://components.omron.com/eu
China
https://components.omron.com.cn
Japan
https://components.omron.com/jp

© OMRON Corporation 2007-2022 All Rights Reserved.
In the interest of product improvement, specifications are subject to change without notice.

Cat. No. B118-E1-04
0922 (0207)

Downloaded from Arrow.com.