



**Part Number :** [714390364](#)

**Product Description :** 1.00mm Mezz (IEEE 1386) Receptacle, Surface Mount, Dual Row, Vertical Stacking, Tube, 0.76µm Gold (Au), 64 Circuits Pick and Place Cap

**Series Number :** 71439

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents and Resources

### Drawings

[714390364 sd.pdf](#)

[PK-70873-014-001.pdf](#)

[PK-70873-063-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


### Specifications

[PS-71436-9999-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Board-to-Board Connectors
Series	71439
Description	1.00mm Mezz (IEEE 1386) Receptacle, Surface Mount, Dual Row, Vertical Stacking, Tube, 0.76µm Gold (Au), 64 Circuits Pick and Place Cap
Application	Board-to-Board, Mezzanine
Component Type	Receptacle
Product Name	1.00mm Mezzanine (IEEE 1386)
UPC	800753784888

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	100V

## Physical

Circuits (Loaded)	64
Circuits (maximum)	64
Color - Resin	Natural
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Mated Height	10.00mm, 8.00mm, 9.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.000/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Surface Mount

## Solder Process Data

Lead-Free Process Capability	REFLOW
Max-Temp	260

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
-------------	-------------

1.00mm Mezz (IEEE 1386) Vertical Plugs	<u>71436</u>
---	--------------

---

This document was generated on May 20, 2026