


Search

Home > Products > Fuses > Axial Radial Thru Hole Fuses > TE5 Fuses > 395 > 39506300440

Print

39506300440 - 395 Series



Series: 395

Fuse 395 Datasheet

Features:

- Reduced PCB space requirements
- Direct solderable or plug-in versions
- Internationally approved
- Low internal resistance
- Shocksafe casing
- Vibration resistant
- Halogen free
- CCCe for China import

Click on part number below for individual TC curve files.

Questions? Contact Littelfuse Support

Check Stock

Order Samples

NEW!
Product Selection Guide eCatalog
[Read Now](#)

Electronics
News and Information
[SIGN UP NOW](#)

Feedback

Electrical Characteristics | **Technical Resources** | Environmental Info

Property (Mouseover for details)	Value
Ampere Rating (A)	0.63
Nominal Melting I ² T (A ² sec)	0.045
Interrupting Rating	100A@125VAC
Min Operating Temp °C	-40
Max Operating Temp (°C)	85
Moisture Sensitivity Level	MIL-STD-202 Method 106
Nominal Power Dissipation (W)	135
Nominal Voltage Drop (mV)	210
Nominal Cold Resistance (Ohms)	0.118
Opening	Fast-Acting (F)
Package Size	TE5 (8.5x8mm)
VAC (V)	125

Connect with Littelfuse

Sign up to receive special offers and news

For more details about how we use your information, check our [Privacy Statement](#).



Mobile Site

About Littelfuse

- About Littelfuse
- Conflict Free Statement
- History
- Investor Relations
- Legal
- Press Room
- Privacy Statement
- Supply Chain Transparency
- Website Feedback

Explore Littelfuse

- Capabilities Brochures
- Careers
- Check Distributor Stock
- Competitor Cross Reference
- Industries
- Order Samples
- Products
- Services

Technical Resources

- Application Designs
- Education
- FAQs
- iDesign™
- Littelfuse University
- Product Catalogs
- Quality Documents
- Technical Documents