




HEAT SHRINK TUBING



✓ Active

TE CONNECTIVITY (TE)
RNF-100-3/4-X-FSP
[Raychem](#) | [RNF-100](#)

RNF-100-3/4-X-FSP
TE Internal Number: 4568284001
Alias ID: 8-1198919-1

[Always EU RoHS/ELV Compliant](#)

Wall Type **Single**

Resistant To **Abrasion**

Product Source **Czech Republic**

Packaging Method **Flat Spool**

Shrink Ratio **2:1**

Catalog Pages/Data Sheets

[RNF-100 Pages From 9-1773447-9](#)
PDF
English

Product Specifications

Product Specification
[RNF-100 Sleeving](#)
PDF
English

Instruction Sheets

Instruction Sheet (U.S.)
[Global Dimensional Life For RAYCHEM Heat Shrink Tubing Standard Size Products \(Customer Distribution\)](#)
PDF
English

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Wall Type	Single
Electrical Characteristics	Voltage (Max) (kV)	.6
Body Features	Shrink Ratio	2:1
	Color	Clear
	Flexibility	Flexible
	Material	Crosslinked Polyolefin

	Fluid Type	Hydraulic Fluid
Dimensions	Recovered Wall Thickness (Nominal)	.76 mm [.03 in]
	Recovered Inside Diameter (Max)	9.5 mm [.374 in]
	Expanded Inside Diameter (Min)	19.1 mm [.75 in]
Usage Conditions	Resistant To	Abrasion
	Recovery Temperature (°C)	121
	Operating Temperature Range (°C)	-55 – 135
	Flammability	Non-Flame-Retardant
	Fluid Resistance	Splash Protection
	Shrink Temperature (Min) (°C)	95
Packaging Features	Packaging Method	Flat Spool
Other	Product Source	Czech Republic
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	