

Specifications



Eaton 170E2098

Fuse-link, high speed, 400 A, AC 500 V, 55 x 55 x 140 mm, aR, IEC, with indicator

General specifications

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170E2098
UPC	051712209021
EAN	5027590438292
PRODUCT LENGTH/DEPTH	280 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	175 mm
PRODUCT WEIGHT	120.6 g
COMPLIANCES	CE RoHS Compliant EAC
CERTIFICATIONS	IEC 60269-4
GLOBAL CATALOG	170E2098
PRODUCT TYPE	High speed square body fuse

Product specifications

AMPERAGE RATING	400 A
BREAKING CAPACITY	220 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	Other
RATED VOLTAGE AC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	110 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	80 W
FUSE SHAPE	Square body, center bolted tags
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	diode protection
FUSE TYPE	Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:

Resources

CATALOGS

[eaton-bussmann-series-iec-high-speed-fuses-catalogue-ca135001en-en-gb.pdf](#)

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

[eaton-high-speed-square-body-fuse-declaration-of-conformity-eu250670en.pdf](#)

MANUALS AND USER GUIDES

[High speed fuses application guide](#)

MCAD MODEL

[eaton-hs-square-body-fuses-mcad-3d-models-u1021.stp](#)

PRODUCT NOTIFICATIONS

[eaton-bussmann-series-170m-fuses-product-change-notice-pcn-bur-00193-en-us.pdf](#)

[eaton-bussmann-series-ukca-marking-high-speed-fuses-pcn-bur-00167-en-gb.pdf](#)



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

