

# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

M23, Cable connector, CA, angled, shielded: yes, SPEEDCON locking, No. of pos.: 8+1, Direction of rotation: Standard, type of contact: Socket, Solder connection, cable diameter range: 3 mm ... 14.5 mm, coding:N Alternative product in accordance with RoHS II without Exemption 6c (Pb <0.1%) 1243560



## Your advantages

- Angled cable outlet for confined spaces
- Can be adapted to various applications, thanks to adjustable cable outlet direction
- Safe use in the field, thanks to high degree of protection
- Connector for flexible on-site assembly
- Consistent EMC protection for reliable transmission of signals
- Reduced connection time with SPEEDCON fast locking system
- Solder connection: proven connection technology for various litz wires

## Commercial Data

Item number	1619442
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to Order (non-returnable)
Sales Key	A12
Product Key	ABRBFH
Catalog Page	Page 90 (C-2-2019)
GTIN	4046356824057
Weight per Piece (including packing)	191.2 g
Weight per Piece (excluding packing)	191.2 g
Customs tariff number	85366990
Country of origin	DE

# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Technical Data

### Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

### Connector

#### Connection 1

Head design	Socket
-------------	--------

#### Insulating body

Coding	N
Insulation body material	PBT
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact type	Socket
Application	Signal
Number of positions	9
Direction of rotation	Standard
Connection profile	8+1
Contact diameter <b>Power contacts</b>	2 mm
Litz wire cross-section <b>Power contacts</b> max.	2.5 mm <sup>2</sup>
Rated current <b>Power contacts</b>	20 A
Rated voltage	48 V AC
	74 V DC
Rated surge voltage	1.5 kV
Overshoot category	III
Degree of pollution	3
Contact diameter <b>Signal contacts</b>	1 mm
Litz wire cross-section <b>Signal contacts</b> max.	1 mm <sup>2</sup>
Nominal current per signal contact	8 A

#### Housing

Housing material	Metal
Type of locking	SPEEDCON locking
Pg screw connection	none
Degree of protection (plugged in)	IP67
Thread type	M23

#### Seal

External cable diameter	3 mm ... 14.5 mm
-------------------------	------------------

# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



Seal material

NBR

## Ambient conditions

Ambient temperature (operation)

-40 °C ... 125 °C

# Cable connector - CA-09S1N12T0DNS


1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Drawings

Dimensional drawing




# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



Schematic diagram



# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Approvals

<b>cUL Recognized</b> Approval ID: E335019-20141210				
	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $mm^2$
Power	48 V	12 A	- 14	-
Signal	48 V	6 A	- 18	-

<b>UL Recognized</b> Approval ID: E335019-20141210				
	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $mm^2$
Power	48 V	20 A	- 14	-
Signal	48 V	8 A	- 18	-

**cULus Recognized**

# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Classifications

### ECLASS

ECLASS-9.0	27440102
ECLASS-10.0.1	27440102
ECLASS-11.0	27440102

### ETIM

ETIM 8.0	EC002635
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

China RoHS

Environmentally Friendly Use Period = 50 years

For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Accessories

### Torque screwdriver

Torque screwdriver - SF-Z0028 - 1607456

<https://www.phoenixcontact.com/us/products/1607456>

Torque screwdriver, series: RC



### Hook wrench

Hook wrench - SF-Z0027 - 1607455

<https://www.phoenixcontact.com/us/products/1607455>

Hook wrench, series: RC



# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Protective cap

Protective cap - RC-Z2058 - 1604223

<https://www.phoenixcontact.com/us/products/1604223>

Plastic protection cap for connectors with M23 knurled nut



---

## Plastic anti-static dust protection cap

Plastic anti-static dust protection cap - RC-Z2468 - 1611796

<https://www.phoenixcontact.com/us/products/1611796>

Plastic protection cap, antistatic, for connectors with M23 knurled nut



# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Color-coding

Color-coding - RF-Z0014 - 1620588

<https://www.phoenixcontact.com/us/products/1620588>

Color-coding, color: green



---

## Color-coding

Color-coding - RF-Z0015 - 1620592

<https://www.phoenixcontact.com/us/products/1620592>

Color-coding, color: orange



# Cable connector - CA-09S1N12T0DNS

1619442

<https://www.phoenixcontact.com/us/products/1619442>



## Color-coding

Color-coding - RF-Z0016 - 1620593

<https://www.phoenixcontact.com/us/products/1620593>

Color-coding, color: black



---

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)